

Rittal – The System.

Faster – better – everywhere.

► Terminal boxes KL without gland plate – KL 1504.510

Date : Aug 10, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Terminal boxes KL without gland plate – KL 1504.510

created: 10.08.2020 on www.rittal.com/com-en



Discontinued article.

This item will be discontinued on: 30.09.2020 |||This item is being replaced by: 1504000

Product description

Material:	Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal
Surface finish:	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4
IK Code:	IK08
Supply includes:	Enclosure with cover Quick-release fastener including plastic bushes
Basic material:	Sheet steel

Product features

Dimensions:	Width: 400 mm Height: 200 mm Depth: 120 mm
Material thickness:	Enclosure: 1.25 mm Cover: 1.25 mm

Packs of:	1 pc(s).
Weight/pack:	3.6 kg
EAN:	4028177251168
Customs tariff number:	85389099
ETIM 7.0:	EC002713
ETIM 6.0:	EC002713
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	KL Terminal box, WHD: 400x200x120 mm, Sheet steel, without mounting plate, with cover, without gland plate
Approvals	
Approvals:	Bureau Veritas CSA DNV-GL Lloyds Register of Shipping RRR Russian Maritime Register of Shipping TÜV UL + C-UL
Certificates:	Certificate of manufacturer according to RMRS EAC IK-Code Protection category
Declarations:	Declaration of conformity