

Rittal – The System.

Faster – better – everywhere.

LED system light – SZ 2500.314

Date : Sep 23, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



LED system light – SZ 2500.314

created: 23.09.2020 on www.rittal.com/com-en



Product description

Design:	with socket, with motion detector
Benefits:	Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application
Equipment:	Motion sensor Socket 90° rotating connector Adjustable light direction Adjustable light distribution
Motion sensor:	yes
Material:	Light body: Extruded aluminium Light cover: Polycarbonate (halogen-free) Light ends: PC-ABS (halogen-free)
Colour:	Enclosure: RAL 7016
Protection category IP to IEC 60 529:	IP 20
Supply includes:	Assembly screws

Product features

Dimensions:	Width: 437 mm Height: 85 mm Depth: 44 mm
--------------------	--

Rated operating voltage:	100 V - 125 V, 1~, 50 Hz/60 Hz
Installation options:	Directly onto the enclosure section with 25 mm pitch pattern
Operating temperature:	Operation (environment): -20 °C...+55 °C
Power consumption:	13 W
Equipment (electrical):	Jack/socket (type): USA/CDN (type B, NEMA 5-15)
Rated insulation voltage:	300 V AC
Rated impulse withstand voltage, phase to earth:	2500 V AC
Luminous flux:	1200 lm
Light colour:	4000 K (neutral white)
Protection class:	II (all-insulated)
Overvoltage category:	II
Connection options:	Infeed, 3-pole Through-wiring, 3-pole
Light – installation type:	Screw-fastening Clip attachment
Packs of:	1 pc(s).
Weight/pack:	0.7 kg
Copper weight (kg per piece):	0
EAN:	4028177811287
Customs tariff number:	94054099
ETIM 7.0:	EC000321
ETIM 6.0:	EC000321
eCl@ss 8.0/8.1:	27189241
eCl@ss 6.0/6.1:	27189241

Product description: SZ System Light LED, 1200 Lumen, L: 437 mm, 100-125 V, with integral motion detector

Approvals

Approvals: CSA
ENEC
UL + C-UL

Certificates: EAC

Declarations: Declaration of conformity