

Rittal – The System.

Faster – better – everywhere.

LED system light – SZ 2500.320

Date : Sep 18, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



LED system light – SZ 2500.320

created: 18.09.2020 on www.rittal.com/com-en



Product description

Design:	With motion detector
Benefits:	Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application
Equipment:	Motion sensor 90° rotating connector Adjustable light direction Adjustable light distribution
Motion sensor:	yes
Material:	Light body: Extruded aluminium Light cover: Polycarbonate (halogen-free) Light ends: PC-ABS (halogen-free)
Colour:	Enclosure: RAL 7016
Protection category IP to IEC 60 529:	IP 20
Supply includes:	Assembly screws

Product features

Dimensions:	Width: 437 mm Height: 85 mm Depth: 37 mm
Rated operating	24 V - 56 V (DC)

voltage:	
Installation options:	Directly onto the enclosure section with 25 mm pitch pattern
Operating temperature:	Operation (environment): -20 °C...+55 °C
Power consumption:	13 W
Luminous flux:	1200 lm
Light colour:	4000 K (neutral white)
Protection class:	II (all-insulated)
Connection options:	Infeed, 2-pole Through-wiring, 2-pole
Light – installation type:	Screw-fastening Clip attachment Magnetic attachment (accessory)
Packs of:	1 pc(s).
Weight/pack:	0.65 kg
Copper weight (kg per piece):	0
EAN:	4028177918818
Customs tariff number:	94054099
ETIM 7.0:	EC000321
ETIM 6.0:	EC000321
eCl@ss 8.0/8.1:	27189241
eCl@ss 6.0/6.1:	27189241
Product description:	SZ System Light LED, 1200 Lumen, L: 437 mm, 24 V DC, with integral motion sensor
Approvals	
Approvals:	CCC UL + C-UL
Certificates:	EAC

Declarations:

Declaration of conformity
