

# Rittal – The System.

Faster – better – everywhere.

► **TopTherm wall-mounted cooling unit  
Blue e Total cooling  
output 2.00 – 4.00 kW  
– SK 3328.540**

Date : Jan 18, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TopTherm wall-mounted cooling unit Blue e Total cooling output 2.00 – 4.00 kW – SK 3328.540

created: 18.01.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Description:</b>	Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller, RiNano coating on the condenser and electrical condensate evaporation as standard.
<b>Benefits:</b>	May be linked to the IoT interface via the Blue e IoT adaptor
<b>Material:</b>	Sheet steel
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	External circuit IP 34 Internal circuit IP 54
<b>Supply includes:</b>	Nano-coated condenser Integral electric condensate evaporation Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts

## Product features

<b>Variant:</b>	wall-mounted
<b>Total cooling output to DIN EN 14511:</b>	L 35 L 35 at 50 Hz: 2.2 kW L 35 L 35 at 60 Hz: 2.55 kW L 35 L 50 at 50 Hz: 1.65 kW L 35 L 50 at 60 Hz: 1.89 kW
<b>Air throughput (unimpeded air flow):</b>	External circuit: 900 m <sup>3</sup> /h Internal circuit: 900 m <sup>3</sup> /h

<b>Rated operating voltage:</b>	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
<b>Dimensions:</b>	Width: 400 mm Height: 1580 mm Depth: 295 mm
<b>Temperature control:</b>	e-Comfort controller (factory setting +35 °C)
<b>Temperature range:</b>	Operation (environment): +10 °C...+55 °C Setting range: +20 °C...+55 °C
<b>Refrigerant/cooling medium:</b>	Refrigerant: R134a Quantity: 950 g Global Warming Potential (GWP): 1430 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 1.36 t
<b>Power consumption P<sub>ej</sub>:</b>	L 35 L 35 at 50 Hz: 0.92 kW L 35 L 35 at 60 Hz: 1.15 kW L 35 L 50 at 50 Hz: 1.15 kW L 35 L 50 at 60 Hz: 1.4 kW
<b>Rated current max.:</b>	At 50 Hz: 2.8 A At 60 Hz: 3.3 A
<b>Start-up current max.:</b>	At 50 Hz: 6.8 A At 60 Hz: 7.8 A
<b>Pre-fuse:</b>	Motor circuit-breaker: 6,3 A...10 A
<b>Permissible operating pressure (p. max.):</b>	28 bar
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	67 kg
<b>EAN:</b>	4028177323063
<b>Customs tariff number:</b>	84158200
<b>ETIM 7.0:</b>	EC000855
<b>ETIM 6.0:</b>	EC000855
<b>eCl@ss 8.0/8.1:</b>	27180704
<b>eCl@ss 6.0/6.1:</b>	27180704
<b>Product description:</b>	SK cooling unit Blue e, wall-mounted, 2.2 kW, 400-460 V, 3~, 50/60 Hz, Sheet steel,

## Approvals

<b>Approvals:</b>	Approval overview UL + C-UL - FTTA UR + C-UR	CCC exception letter CSA
<b>Certificates:</b>	EAC	
<b>Declarations:</b>	Declaration of conformity Declaration of conformity - F-gas regulation	