

Rittal – The System.

Faster – better – everywhere.

▶ SE 8 free-standing enclosure system – SE 5840.500

Date : Oct 16, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 8 free-standing enclosure system – SE 5840.500

created: 16.10.2019 on www.rittal.com/com-en



Product description

Material:	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish:	Enclosure, door and rear panel: dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12 NEMA 3R
IK Code:	IK10
Supply includes:	Enclosure, solid top and sides Door(s) R/h door hinge with single-door enclosures, may be swapped to opposite side Mounting plate Gland plates Rear panel, detachable Lock: 3 mm double-bit 2 TS punched rails 18 x 38 mm Rear panel, one-piece
Product modification:	TS 8 and the SE 8 both come with the new mounting plate of the baying enclosure system VX25.

Basic material: Sheet steel

Product features

Dimensions: Width: 1000 mm
Height: 1800 mm
Depth: 400 mm

Mounting plate: Width: 899 mm
Height: 1696 mm

Number of doors: 2

Packs of: 1 pc(s).

Weight/pack: 145 kg

EAN: 4028177666481

Customs tariff number: 94032080

ETIM 6.0: EC000261

ETIM 5.0: EC000261

eCl@ss 8.0/8.1: 27180101

eCl@ss 7.0/7.1: 27180101

eCl@ss 6.0/6.1: 27180101

eCl@ss 5.1/5.1.4: 27180101

Product description: SE Free-standing enclosure system, WHD: 1000x1800x400 mm, Sheet steel, with mounting plate, two doors at the front

Approvals

Approvals: UL + C-UL

Certificates: IK-Code
Protection category
Surface finish

Declarations: Declaration of conformity