

Rittal – The System.

Faster – better – everywhere.

One-piece consoles TP – TP 6746.500

Date : Nov 30, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



One-piece consoles TP – TP 6746.500

created: 30.11.2020 on www.rittal.com/com-en



Discontinued article.

This item will be discontinued on: 31.01.2021 |||This item is being replaced by: 6746600

Product description

Material:	Enclosure: Sheet steel 1.5 mm Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel, 3.0 mm
Surface finish:	Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
IK Code:	IK08
Supply includes:	Enclosure, solid back and sides Door or double door at front, with locking rod Mounting plate Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right Open base for individual cable entry
Note:	With the two-door variant, the base opening is divided in two, and two packs of gland plates are required.
Basic material:	Sheet steel

Product features

Dimensions: Width: 600 mm
Height: 973 mm
Depth (top): 520 mm
Depth (bottom): 400 mm

Mounting plate: Width: 530 mm
Height: 900 mm

Number of doors: 1

Packs of: 1 pc(s).

Weight/pack: 50 kg

EAN: 4028177601192

Customs tariff number: 94032080

ETIM 7.0: EC000784

ETIM 6.0: EC000784

eCl@ss 8.0/8.1: 27180504

eCl@ss 6.0/6.1: 27180504

Product description: TP One-piece console, WHD1: 600x960x400/T2: 520 mm, Sheet steel

Approvals

Approvals: RRR
UL + C-UL

Certificates: IK-Code

Declarations: Declaration of conformity