

Rittal – The System.

Faster – better – everywhere.

PSM socket modules – DK 7856.080

Date : Sep 27, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PSM socket modules – DK 7856.080

created: 27.09.2020 on www.rittal.com/com-en



Product description

Design: non-switchable

Description: The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.

Material: Section: Aluminium, anodised
Socket inserts: Plastic (PA6 GF 30 V1)

Product features

Sockets: 6 x IEC 320 socket C13 - Black

Required number of module slots: 1

Dimensions: Length: 250 mm

Infeeds: Phases per infeed: 1~

Type of electrical connection: WAGO WINSTA MIDI

Thermal overcurrent protection: –

Packs of: 1 pc(s).

Weight/pack: 0.33 kg

Copper weight (kg per piece):	0
EAN:	4028177402539
Customs tariff number:	85369001
ETIM 7.0:	EC000330
ETIM 6.0:	EC000330
eCl@ss 8.0/8.1:	27142604
eCl@ss 6.0/6.1:	27142604
Product description:	DK PSM Plus socket module, C13, 6-way, black, non-switchable
Approvals	
Approvals:	UR + C-UR
Certificates:	EAC
Declarations:	Declaration of conformity