

Rittal – The System.

Faster – better – everywhere.

► **Punched section with
mounting flange, 14 x
39 mm for VX, TS, SE,
PC, IW, AX – VX
8619.790**

Date : Apr 11, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Punched section with mounting flange, 14 x 39 mm for VX, TS, SE, PC, IW, AX – VX 8619.790

created: 11.04.2021 on www.rittal.com/com-en



Product description

Description:	For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.
Material:	Sheet steel
Surface finish:	Zinc-plated
Assembly instruction:	For installation in AX sheet steel, only in conjunction with rail for interior installation AX For installation in AX stainless steel, only in conjunction with perforated door strip
Supply includes:	Assembly parts
Note:	For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required

Product description

To fit:	Enclosure type: VX Enclosure type: TS Enclosure type: SE Enclosure type: AX Enclosure type: AX with locking rod Width/height/depth: 760 mm
Installation options:	On identical punched sections with mounting flanges In the AX sheet steel, in the enclosure door with 3-point lock system in the lockable door
Distance between attachment points:	635 mm

Packs of:	4 pc(s).
Weight/pack:	1.36 kg
Copper weight (kg per piece):	0
EAN:	4028177940765
Customs tariff number:	73269098
ETIM 7.0:	EC002625
ETIM 6.0:	EC002625
eCl@ss 8.0/8.1:	27189234
eCl@ss 6.0/6.1:	23159101
Product description:	VX Punched section with mounting flange, 14 x 39 mm , for door width: 760 mm