

Rittal – The System.

Faster – better – everywhere.

Component adaptor 3- pole – SV 9635.330

Date : Oct 22, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Component adaptor 3-pole – SV 9635.330

created: 22.10.2019 on www.rittal.com/com-en



Product description

Function principle:	For mechanical attachment and direct contacting of electrical equipment on the board
Material:	Polyamide Fire protection corresponding to UL 94-V0
Colour:	RAL 7035
Note:	The technical data may vary for UL applications

Product features

Design:	Comfort
Number of poles:	3-pole
Dimensions:	Width: 45 mm Height: 160 mm Depth: 34.5 mm
Rated current max.:	16 A
Rated operating voltage:	690 V (AC), 3~ 600 V (DC), 3~
Electrical ratings UL:	Rated current (UL): 12 A Rated operating voltage: 600 V AC SCCR: 5 kA
Connection cable:	Cross-section: AWG 14

Length: 120 mm

Design:	Comfort
Number of support rails:	1
Height of support rails:	10 mm
Support rail type:	adjustable
Packs of:	4 pc(s).
Copper weight (kg per piece):	0.01
EAN:	4028177817357
Customs tariff number:	85369095
ETIM 6.0:	EC001531
ETIM 5.0:	EC001531
eCl@ss 8.0/8.1:	27370304
eCl@ss 7.0/7.1:	27370304
eCl@ss 6.0/6.1:	27370304
eCl@ss 5.1/5.1.4:	27370302
Product description:	SV Component adaptor (Comfort), 16 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 14 (L: 120 mm), WH: 45x160 mm
Approvals	
Approvals:	UL + C-UL
Declarations:	Declaration of conformity