

# Rittal – The System.

Faster – better – everywhere.

## **Component adaptor 3- pole – SV 9635.330**

Date : Sep 27, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Component adaptor 3-pole – SV 9635.330

created: 27.09.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Function principle:</b>	For mechanical attachment and direct contacting of electrical equipment on the board
<b>Material:</b>	Polyamide Fire protection corresponding to UL 94-V0
<b>Colour:</b>	RAL 7035
<b>Note:</b>	The technical data may vary for UL applications

## Product features

<b>Design:</b>	Comfort
<b>Number of poles:</b>	3-pole
<b>Dimensions:</b>	Width: 45 mm Height: 160 mm Depth: 34.5 mm
<b>Rated current max.:</b>	16 A
<b>Rated operating voltage:</b>	690 V (AC), 3~ 600 V (DC), 3~
<b>Electrical ratings UL:</b>	Rated current (UL): 12 A Rated operating voltage: 600 V AC SCCR: 5 kA
<b>Connection cable:</b>	Cross-section: AWG 14

Length: 160 mm

<b>Design:</b>	Comfort
<b>Number of support rails:</b>	1
<b>Height of support rails:</b>	10 mm
<b>Support rail type:</b>	adjustable
<b>Packs of:</b>	4 pc(s).
<b>Copper weight (kg per piece):</b>	0.01
<b>EAN:</b>	4028177817357
<b>Customs tariff number:</b>	85369095
<b>ETIM 7.0:</b>	EC001531
<b>ETIM 6.0:</b>	EC001531
<b>eCl@ss 8.0/8.1:</b>	27370304
<b>eCl@ss 6.0/6.1:</b>	27370304
<b>Product description:</b>	SV Component adaptor (Comfort), 16 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 14 (L: 120 mm), WH: 45x160 mm
<b>Approvals</b>	
<b>Declarations:</b>	Declaration of conformity