

Rittal – The System.

Faster – better – everywhere.

Partial doors for TS – SV 9672.164

Date : Oct 16, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Partial doors for TS – SV 9672.164

created: 16.10.2019 on www.rittal.com/com-en



Discontinued article.

This item will be discontinued on: 15.02.2019 |||This item is being replaced by: 9682164

Product description

Description: Suitable for TS enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame SZ 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type F, and from 600 mm height, for comfort handle.

Material: Sheet steel, 2 mm

Surface finish: Textured paint

Colour: RAL 7035

**Protection category
IP to IEC 60 529:** IP 54 for a completed enclosure

Supply includes: Cross member
Hinges
Lock components
Assembly parts

Product features

To fit: Width: = 600 mm

Dimensions: Width: 600 mm
Height: 400 mm

Packs of:	1 pc(s).
Weight/pack:	5.35 kg
Copper weight (kg per piece):	0
EAN:	4028177697713
Customs tariff number:	94039010
ETIM 6.0:	EC000747
ETIM 5.0:	EC000747
eCl@ss 8.0/8.1:	27182204
eCl@ss 7.0/7.1:	27182290
eCl@ss 6.0/6.1:	27182290
eCl@ss 5.1/5.1.4:	27189217
Product description:	SV Partial door, WH: 600x400 mm, for TS