

EASILY CONVERTED.



Width	Base/plinth TS, sheet steel				Flex-Block, plastic, RAL 9005			NEW: Sheet steel, RAL 9005	
100 base/plinth system	Base/plinth components				Base/plinth components			Base/plinth components	
	RAL 7022	Type	RAL 7035	Type	Trim panels	Type	Corner pieces	Trim panels + Corner pieces	Type
300	8601.915	solid	8601.905	solid	8100.300	solid	8100.000	8620.000	solid
400	8601.400	solid	-	-	8100.400	solid		8620.001	solid
500	-	-	-	-	8100.500	solid		-	-
600	8601.600	solid	8601.605	solid	8100.600	solid		8620.002	-
	-	-	7825.601	vented	8100.602	vented		8620.002 + 8620.090*	solid + trim panel vented
	-	-	-	-	8100.605	Brush strip		8620.002 + 8620.092	solid + trim panel with brush strip
800	8601.800	solid	8601.805	solid	8100.800	solid		8620.003	solid
	-	-	7825.801	vented	8100.802	vented		8620.003 + 8620.091*	solid + trim panel vented
	-	-	-	-	8100.805	Brush strip		8620.003 + 8620.093	solid + trim panel with brush strip
850	8601.850	solid	-	-	-	-		8620.004	-
1000	8601.000	solid	-	-	8100.010	solid	8100.000	8620.005	solid
	-	-	-	-	8100.105	Brush strip		8620.005 + 8620.094	solid + trim panel with brush strip
1100	8601.300	solid	-	-	-	-	-	8620.006	-
1200	8601.200	solid	-	-	8100.120	solid	8100.000	8620.007	solid
	-	-	-	-	8100.125	Brush strip		8620.007 + 8620.095	solid + trim panel with brush strip
1600	8601.920	solid	-	-	8100.160	solid	-	8620.008	solid
1800	8601.980	solid	-	-	8100.180	solid	-	8620.009	solid

200 base/plinth system	Base/plinth components				Base/plinth components			Base/plinth components	
	RAL 7022	Type	RAL 7035	Type	Trim panels	Type	Corner pieces	Trim panels + Corner pieces	Type
300	8602.915	solid	8602.905	solid	8200.300	solid	8200.000	8620.020	solid
400	8602.400	solid	-	-	8200.400	solid		8620.021	solid
500	-	-	-	-	8200.500	solid		-	-
600	8602.600	solid	8602.605	solid	8200.600	solid		8620.022	solid
800	8602.800	solid	8602.805	solid	8200.800	solid		8620.023	solid
850	8602.850	solid	-	-	-	-	-	2 x 8620.004	solid
1000	8602.000	solid	-	-	8200.010	solid	8200.000	8620.024	solid
1100	8602.100	solid	-	-	-	-	-	2 x 8620.006	solid
1200	8602.200	solid	-	-	8200.120	solid	8200.000	8620.025	solid
1600	8602.920	solid	-	-	-	-	-	8620.026	solid
1800	8602.980	solid	-	-	-	-	-	8620.027	solid



Depth	Base/plinth TS, sheet steel		Flex-Block, plastic, RAL 9005		NEW: Sheet steel, RAL 9005	
100 base/plinth trim panels	RAL 7022	RAL 7035	Trim panels	Type	Trim panels	Type
300	8601.030	-	8100.300	solid	8620.030	solid
400	8601.040	-	8100.400	solid	8620.031	solid
500	8601.050	-	8100.500	solid	8620.032	solid
600	8601.060	8601.065	8100.600	solid	8620.033	solid
	-	-	8100.605	Brush strip	8620.092	Brush strip
	-	-	8100.602	vented	8620.090	vented
800	8601.080	8601.085	8100.800	solid	8620.034	solid
	-	-	8100.805	Brush strip	8620.093	Brush strip
	-	-	8100.802	vented	8620.091	vented
1000	-	8601.015	8100.010	solid	8620.035	solid
	-	-	8100.105	Brush strip	8620.094	Brush strip
1200	-	8601.025	8100.120	solid	8620.036	solid
	-	-	8100.125	Brush strip	8620.095	Brush strip
200 base/plinth trim panels	RAL 7022	RAL 7035	Trim panels	Type	Trim panels	Type
300	8602.030	-	8200.300	solid	8620.040	solid
400	8602.040	-	8200.400	solid	8620.041	solid
500	8602.050	-	8200.500	solid	8620.042	solid
600	8602.060	8602.065	8200.600	solid	8620.043	solid
800	8602.080	8602.085	8200.800	solid	8620.044	solid
1000	-	8602.015	8200.010	solid	8620.045	solid
1200	-	8602.025	8200.020	solid	8620.046	solid

* Vented trim panels are supplied without corner pieces and can be used for the width and depth.