

Rittal – The System.

Faster – better – everywhere.

 – **DK 7831.453**

Date : 2020.09.21

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



– DK 7831.453

created: 21.09.2020 build on www.rittal.com/hr-hr



Discontinued article.

: 31.12.2019

Product description

Benefits:	Robust frame structure Front and rear door vented across the entire surface Open surface area > 78 % perforated 2-point locking Door hinge may be swapped to opposite side without machining Cable entry via the base/plinth and roof (optional) Bayable at all levels Static load capacity of up to 1000 kg
Material:	Čelični lim
Surface finish:	Enclosure frame: Dipcoat-primed Enclosure panels: Dipcoat-primed, powder-coated Mounting angles, mounting frame and punched sections with mounting flanges: Zinc-plated, passivated
Colour:	RAL 7035
Supply includes:	Nožice za niveliranje
Note on Model No.:	Extended delivery times.

Product features

Dimensions:	Width: 600 mm Height: 2200 mm Depth: 1000 mm
--------------------	--

Installation height for components per door:	21 U
Distance between levels as delivered:	740 mm
Number of doors:	Front: 2 Rear: 2
Packs of:	1 pc(s).
Weight/pack:	173,5 kg
EAN:	4028177642713
Customs tariff number:	94032080
ETIM 7.0:	EC002499
ETIM 6.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 6.0/6.1:	27180207