

Rittal – The System.

Faster – better – everywhere.

– VX 8840.110

Date : 2020.09.28

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



– VX 8840.110

created: 28.09.2020 build on www.rittal.com/hr-hr



Product description

Material:	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Glazed door: Single-pane safety glass, 3 mm Rear door: Sheet steel, 2.0 mm Gland plates: Sheet steel, 1.5 mm
Surface finish:	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
IK Code:	IK08
Supply includes:	Krovni lim
Basic material:	Čelični lim

Product features

Dimensions:	Width: 800 mm Height: 2000 mm Depth: 800 mm
Packs of:	1 pc(s).
Weight/pack:	90 kg

EAN: 4028177951358

Customs tariff number: 94032080

ETIM 7.0: EC000261

ETIM 6.0: EC000261

eCI@ss 8.0/8.1: 27180101

eCI@ss 6.0/6.1: 27180101

Product description: VX Baying enclosure system, WHD: 800x2000x800 mm, sheet steel, without mounting plate, glazed door at the front

Approvals

Approvals: CSA
Lloyds Register of Shipping
UL + C-UL

Declarations: Declaration of conformity
