

Rittal – The System.

Faster – better – everywhere.

► NV účinski rastavljač, vel. 00 do 3 s elektroničkom nadzornom jedinicom (ESÜ) – SV 9344.020

Date : 2020.09.29

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



NV učinski rastavljač, vel. 00 do 3 s elektroničkom nadzornom jedinicom (ESÜ) – SV 9344.020

created: 29.09.2020 build on www.rittal.com/hr-hr



Product description

Material: Polyamide
Fire protection corresponding to UL 94-V0
Contact tracks: Electrolytic copper, silver-plated

Colour: Chassis: RAL 7035
Cover: RAL 7035/7001

Basis of test: IEC/DIN EN 60 947-3
DIN EN 60 269-2 (fuse inserts)

Product features

Design: Size: 00

Number of poles: 3-pole

For mounting plate assembly: da

Dimensions: Width: 106 mm
Height: 194 mm

Type of electrical connection: Box terminal

Rated operating voltage: 400 V - 690 V, 3~

Clamping area for laminated copper bars: Width: 13 mm
Height: 13 mm

Connection for round conductor cross-sections:	4 mm ² - 95 mm ²
Rated operating current max.:	160 A
Cable outlet:	Top/bottom
Packs of:	1 pc(s).
Weight/pack:	0,86 kg
Copper weight (kg per piece):	0,15
EAN:	4028177540521
Customs tariff number:	85369095
ETIM 7.0:	EC001040
ETIM 6.0:	EC001040
eCl@ss 8.0/8.1:	27371401
eCl@ss 6.0/6.1:	27371401
Product description:	SV NH fuse-switch disconnecter, size 00, 160 A, 400-690 V, 3-pole, box terminal, with electronic fuse monitoring, for mounting plate assembly
Approvals	
Certificates:	EAC
Declarations:	Declaration of conformity