

Rittal – The System.

Faster – better – everywhere.

– SV 9682.166

Date : 2020.09.28

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



– SV 9682.166

created: 28.09.2020 build on www.rittal.com/hr-hr



Product description

Description: Suitable for VX enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type A.

Material: Sheet steel, 2 mm

Surface finish: Textured paint

Colour: RAL 7035

**Protection category
IP to IEC 60 529:** IP 54

Supply includes: Razdjelnik
Panti
Dijelovi za zaključavanje

Note: Opening angle of partial doors max. 130°

Product features

To fit: Width: = 600 mm

Dimensions: Width: 600 mm
Height: 600 mm

Number of locks: 2

Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177928961
Customs tariff number:	94039010
ETIM 7.0:	EC000747
ETIM 6.0:	EC000747
eCl@ss 8.0/8.1:	27182204
eCl@ss 6.0/6.1:	27182290
Product description:	VX Partial door, WH: 600x600 mm sheet steel
Approvals	
Approvals:	UL + C-UL