

Rittal – The System.

Faster – better – everywhere.

► Stepped collar For wall thicknesses from 1.5 to 4.5 mm – SZ 2899.250

Date : Sep 27, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Stepped collar For wall thicknesses from 1.5 to 4.5 mm – SZ 2899.250

created: 27.09.2020 build on www.rittal.com/il-en



Product description

Description: For cable entry, simply cut off at the required level to match the cable diameter.

Applications: For wall thicknesses from 1.5 to 4.5 mm

Material: Plastic to UL 94-HB

**Protection category
IP to IEC 60 529:** IP 54 with careful cable entry

Product features

Thread: Type: M25

**For material
thicknesses:** 1,5 mm - 4,5 mm

Min. cable diameter: 5 mm

Max. cable diameter: 21 mm

Packs of: 50 pc(s).

Weight/pack: 0.15 kg

**Copper weight (kg
per piece):** 0

EAN: 4028177389618

Customs tariff number:	39269097
ETIM 7.0:	EC000879
ETIM 6.0:	EC000879
eCl@ss 8.0/8.1:	27069216
eCl@ss 6.0/6.1:	27400604
Product description:	SZ Stepped collar, for wall thickness from 1,5 bis 4,5 mm, for hole M25, Sealing range: 5-21 mm
Approvals	
Certificates:	EAC