

# Rittal – The System.

Faster – better – everywhere.

## ► Splitter hole punch, round for sheet steel, with triple splitting – **AS 4055.560**

Date : Apr 20, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Splitter hole punch, round for sheet steel, with triple splitting – AS 4055.560

created: 20.04.2021 build on [www.rittal.com/il-en](http://www.rittal.com/il-en)



## Product description

<b>Design:</b>	With triple splitting
<b>Description:</b>	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
<b>Note:</b>	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
<b>Supply includes:</b>	Female dies Male dies
<b>Note:</b>	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel

## Product description

<b>PG size:</b>	48
<b>Ø punch:</b>	60 mm
<b>Tension screw (Ø x L):</b>	19 mm x 75 mm
<b>Hydraulic tension screw Ø:</b>	19 mm
<b>Hydraulic tension screw Model No.:</b>	4055.663
<b>Maximum</b>	3 mm

**machinable material  
thickness, sheet steel:**

<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	0.84 kg
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177808805
<b>Customs tariff number:</b>	82073010
<b>ETIM 7.0:</b>	EC000156
<b>ETIM 6.0:</b>	EC000156
<b>eCl@ss 8.0/8.1:</b>	21049047
<b>eCl@ss 6.0/6.1:</b>	21040702
<b>Product description:</b>	Splitter hole punch, round for sheet steel, with triple splitting