

Rittal – The System.

Faster – better – everywhere.

▶ WM Stainless Wallmount Enclosures



Rittal WM stainless steel enclosures can be used for virtually any application. NEMA 4X protection ratings are ensured through a secure locking system, foamed-in-place gasket and knife-edge perimeter. Features include a body constructed of cold rolled steel, steel doors and zinc-plated mounting panels. WM enclosures are readily available in all of the most popular sizes, protection categories and configurations – including universal disconnect cutout – and a full range of accessories. For complete details on the entire line, go to www.rittal.us.

- One-piece welded stainless steel body
- Available 304 and 316L stainless steel
- Flange-trough collar opening channels liquids and dust away from enclosure gasket and enclosure interior
- Left-hand hinged door
- Blind riv-nuts allow for secure mounting
- Foamed-in-place gasket
- Zinc-plated mounting panel standard
- Enclosures less than 20" in height have one ¼ turn latch
- Enclosures 20 - 40" in height have two ¼ turn latches
- Enclosures greater than or equal to 42" in height have a 3-point latching L-handle
- Disconnect enclosures have a 2 or 3-point latching L-handle

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



304 Stainless Steel – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
8017620	WM121206N4	12x12x6
8017614	WM161206N4	16x12x6
8017610	WM161606N4	16x16x6
8017613	WM201606N4	20x16x6
8017616	WM202006N4	20x20x6
8017608	WM161208N4	16x12x8
9851532	WM161608N4	16x16x8
8017605	WM201608N4	20x16x8
8018478	WM202008N4	20x20x8
8017621	WM241608N4	24x16x8
8017603	WM242008N4	24x20x8
8017600	WM242408N4	24x24x8
8017607	WM302408N4	30x24x8
8017611	WM303008N4	30x30x8
8017618	WM362408N4	36x24x8
8017615	WM363008N4	36x30x8
8017622	WM242010N4	24x20x10
8018493	WM302410N4	30x24x10
8018903	WM303010N4	30x30x10
8017619	WM363010N4	36x30x10
8018514	WM483610N4	48x36x10
8018474	WM242412N4	24x24x12
8017612	WM302412N4	30x24x12
8017606	WM363012N4	36x30x12
8017602	WM363612N4	36x36x12
8017617	WM423612N4	42x36x12
8017601	WM483612N4	48x36x12
8017604	WM603612N4	60x36x12
8018500	WM363016N4	36x30x16
8018515	WM483616N4	48x36x16
8018521	WM603616N4	60x36x16

304 Stainless Steel, 3-point Latch – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
9851500	WM242008N43PT	24x20x8
9851501	WM242408N43PT	24x24x8
9851504	WM302408N43PT	30x24x8
9851505	WM303008N43PT	30x30x8
9851507	WM362408N43PT	36x24x8
9851508	WM363008N43PT	36x30x8
9851502	WM242010N43PT	24x20x10
9851529	WM302410N43PT	30x24x10
9851509	WM363010N43PT	36x30x10
9851503	WM242412N43PT	24x24x12
9851506	WM302412N43PT	30x24x12
9851510	WM363012N43PT	36x30x12
9851511	WM363612N43PT	36x36x12
9851527	WM363016N43PT	36x30x16

304 Stainless Steel Disconnect – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
8018627	WM242608X4	24x26x8
8018628	WM363208X4	36x32x8
8018632	WM363210X4	36x32x10
8018635	WM603810X4	60x38x10
8018633	WM363212X4	36x32x12
8018629	WM423212X4	42x32x12
8018630	WM483812X4	48x38x12
8018631	WM603812X4	60x38x12
8018634	WM483816X4	48x38x16

Note: Mounting panel included with all WM enclosures.
Measurements are approximate.

316L Stainless Steel – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
8018525	WM121206N6	12x12x6
8017636	WM161206N6	16x12x6
8017638	WM161606N6	16x16x6
8017639	WM201606N6	20x16x6
8018529	WM202006N6	20x20x6
8017644	WM161208N6	16x12x8
9851531	WM161608N6	16x16x8
8017628	WM201608N6	20x16x8
8017624	WM202008N6	20x20x8
8018532	WM241608N6	24x16x8
8017632	WM242008N6	24x20x8
8017623	WM242408N6	24x24x8
8017625	WM302408N6	30x24x8
8018546	WM303008N6	30x30x8
8017643	WM362408N6	36x24x8
8017642	WM363008N6	36x30x8
8018534	WM242010N6	24x20x10
8017634	WM302410N6	30x24x10
8018904	WM303010N6	30x30x10
8018552	WM363010N6	36x30x10
8017641	WM483610N6	48x36x10
8017627	WM242412N6	24x24x12
8017637	WM302412N6	30x24x12
8017630	WM363012N6	36x30x12
8017629	WM363612N6	36x36x12
8018564	WM423612N6	42x36x12
8017626	WM483612N6	48x36x12
8017631	WM603612N6	60x36x12
8017635	WM363016N6	36x30x16
8017640	WM483616N6	48x36x16
8017633	WM603616N6	60x36x16

316 Stainless Steel, 3-point Latch – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
9851512	WM242008N63PT	24x20x8
9851513	WM242408N63PT	24x24x8
9851516	WM302408N63PT	30x24x8
9851517	WM303008N63PT	30x30x8
9851519	WM362408N63PT	36x24x8
9851520	WM363008N63PT	36x30x8
9851514	WM242010N63PT	24x20x10
9851530	WM302410N63PT	30x24x10
9851521	WM363010N63PT	36x30x10
9851515	WM242412N63PT	24x24x12
9851518	WM302412N63PT	30x24x12
9851522	WM363012N63PT	36x30x12
9851523	WM363612N63PT	36x36x12
9851528	WM363016N63PT	36x30x16

316L Stainless Steel Disconnect – UL/cUL Type 12, 3R, 4, 4X

Part No.	Catalog No.	H x W x D
8018636	WM242608X6	24x26x8
8018637	WM363208X6	36x32x8
8018641	WM363210X6	36x32x10
8018644	WM603810X6	60x38x10
8018642	WM363212X6	36x32x12
8018638	WM423212X6	42x32x12
8018639	WM483812X6	48x38x12
8018640	WM603812X6	60x38x12
8018643	WM483816X6	48x38x16