

Rittal – The System.

Faster – better – everywhere.

▶ WKDH Deep-Hinged Window Kit



It's plain to see why you need Rittal's Deep-Hinged Window Kit.

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust.

The polycarbonate window offers advanced UV blocking technology that promotes outdoor weathering performance and resistance to color shift.

This deep-hinged window kit is aesthetically appealing and fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. WKDH overall depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting.

Rittal's WKDH is FTTA UL Listed and rated for UL Type 12/3R/4 for carbon steel and 12/3R/4X for stainless steel.

For complete details on the entire line, visit www.rittal.us.

- UL Listed, Type 12/3R/4/4X
- Available in carbon, 304 and 316L stainless steel
- Foamed-in-place gasket
- 1/4 turn latch for quick and easy access
- Quick-release hidden 130° door hinges
- Designed for either left or right hinging
- Electrophoresis dip-coat primer with powder-coat surface for carbon steel WKDH version
- Flange-trough collar opening channels liquids and dust away from gasket and interior
- 1/4" thick flush mounted polycarbonate viewing window for clear visibility
- Advanced UV resistant window for long-lasting outdoor performance
- Full-size drill template for easy mounting included
- 2.75"/70mm deep to allow for extra deep pushbuttons

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



WKDH Deep-Hinged Window Kit

Catalog Part Number	HxW		Viewing Area		Material
	in.	mm.	in.	mm	
WKDH1212C	12x12	300x300	7.9x4.9	200x125	Carbon Steel
WKDH1216C	12x16	300x400	7.9x8.9	200x225	Carbon Steel
WKDH1418C	14x18	350x450	9.8x10.8	250x275	Carbon Steel
WKDH1422C	14x22	350x550	9.8x14.8	250x375	Carbon Steel
WKDH1612C	16x12	400x300	11.8x4.9	300x125	Carbon Steel
WKDH2016C	20x16	500x400	15.7x8.9	400x225	Carbon Steel
WKDH2416C	24x16	600x400	19.7x8.9	500x225	Carbon Steel
WKDH2420C	24x20	600x500	19.7x12.8	500x325	Carbon Steel
WKDH3024C	30x24	760x600	26.0x16.3	660x415	Carbon Steel
WKDH3624C	36x24	900x600	30.7x16.3	780x415	Carbon Steel
WKDH12124	12x12	300x300	7.9x4.9	200x125	304 Stainless Steel
WKDH12164	12x16	300x400	7.9x8.9	200x225	304 Stainless Steel
WKDH14184	14x18	350x450	9.8x10.8	250x275	304 Stainless Steel
WKDH14224	14x22	350x550	9.8x14.8	250x375	304 Stainless Steel
WKDH16124	16x12	400x300	11.8x4.9	300x125	304 Stainless Steel
WKDH20164	20x16	500x400	15.7x8.9	400x225	304 Stainless Steel
WKDH24164	24x16	600x400	19.7x8.9	500x225	304 Stainless Steel
WKDH24204	24x20	600x500	19.7x12.8	500x325	304 Stainless Steel
WKDH30244	30x24	760x600	26.0x16.3	660x415	304 Stainless Steel
WKDH36244	36x24	900x600	30.7x16.3	780x415	304 Stainless Steel
WKDH12126	12x12	300x300	7.9x4.9	200x125	316L Stainless Steel
WKDH12166	12x16	300x400	7.9x8.9	200x225	316L Stainless Steel
WKDH14186	14x18	350x450	9.8x10.8	250x275	316L Stainless Steel
WKDH14226	14x22	350x550	9.8x14.8	250x375	316L Stainless Steel
WKDH16126	16x12	400x300	11.8x4.9	300x125	316L Stainless Steel
WKDH20166	20x16	500x400	15.7x8.9	400x225	316L Stainless Steel
WKDH24166	24x16	600x400	19.7x8.9	500x225	316L Stainless Steel
WKDH24206	24x20	600x500	19.7x12.8	500x325	316L Stainless Steel
WKDH30246	30x24	760x600	26.0x16.3	660x415	316L Stainless Steel
WKDH36246	36x24	900x600	30.7x16.3	780x415	316L Stainless Steel



Rittal North America LLC
 Woodfield Corporate Center
 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173 • USA
 Phone: 937-399-0500 • Toll-free: 800-477-4000
 Email: rittal@rittal.us • Online: www.rittal.us



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES