


8		9		10	
REV	CHANGE DESCRIPTION	DATE	BY	ECN	
01	ADDED NOTE 3, MAXIMUM LOAD	1/17/19	DL	3525	

Note:

1. Feet with mounting holes are for top of enclosure.
2. Feet with slots are for bottom of enclosure.
3. Tab on feet wraps around side of enclosure.
4. Feet are in sets of four.
5. Maximum symmetrical load for four brackets is 350lb



***NOTE: ONLY IMAGE INSIDE RECTANGLE SHOULD BE PRINTED AS INSTRUCTIONS**

<p>This drawing contains proprietary and confidential information of Rittal and must be used strictly in accordance with the limited purpose for which it was submitted. Any reproduction, disclosure, or use of this drawing is expressly prohibited unless approved by Rittal in writing.</p>									
1	2	3	4	5	6	7	8	9	10
<p>DO NOT SCALE DRAWING ASME Y14.5M-1994 SCALE = 0.180</p>									
<p>MATERIAL: TYPE: FINISH:</p>									
<p>UNLESS OTHERWISE SPECIFIED</p>									
<p>(FORMS AND PLANS ONLY)</p>									
<p>TOLERANCES</p>									
<p>UNLESS OTHERWISE SPECIFIED</p>									
<p>INCH</p>									
<p>0.000</p>									
<p>0.005</p>									
<p>0.010</p>									
<p>0.020</p>									
<p>0.030</p>									
<p>0.060</p>									
<p>0.125</p>									
<p>ALL INSIDE ROUN TO BE 0.030 INCH</p>									
<p>FORMING TOLERANCES</p>									
<p>0.000</p>									
<p>0.005</p>									
<p>0.010</p>									
<p>0.020</p>									
<p>0.030</p>									
<p>0.060</p>									
<p>0.125</p>									
<p>ANGLES</p>									
<p>±1.0°</p>									
<p>±1.0°</p>									
<p>DATE NAME CUSTOMER DWG #</p>									
<p>02/28/00 LSG000</p>									
<p>WEIGHT:</p>									
<p>ZZB #:</p>									
<p>DESCRIPTION:</p>									
<p>Mounting Foot Locations</p>									
<p>WMMFL</p>									
<p>007</p>									
<p>301 West Wacker St</p>									
<p>Fremont, IL 60137</p>									