

Rittal – The System.

Faster – better – everywhere.

► TS IT Pro Network/Server Enclosures



Easy to Order - Ready to Ship

One part number complete with a full feature set with everything needed for fast and easy deployment available at multiple locations throughout the U.S. Ships complete with perforated single front door and split rear doors keyed alike, quick release security hinges, leveling feet, casters, roof with brush baffle cable access channels, vertical cable walls with dual PDU mountings, and half height lockable quick release sidewalls.



Flexible and Innovative

The TS IT Pro is designed to meet a variety of customer requirements, including “ship-loadable” for transporting equipped racks to its destination. Intelligent air flow management increase the efficiency of your installation and ensures sustainable operation.

A wide range of security and access control, as well as cable and air flow management accessories are available to create a robust solution.

The strength and rigidity of the TS IT Pro has a static load capacity of 3,750 lbs. and a dynamic capacity of 2,250 lbs. which enables fully integrated systems to ship ready for deployment.

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



TS IT Pro with Sidewalls

Part Number	9982.202	9982.206	9982.204	9982.208	9982.210	9982.214	9982.212	9982.216
RU Height	42U	42U	42U	42U	48U	48U	48U	48U
Height inches (mm)	79" (2012)	79" (2012)	79" (2012)	79" (2012)	90" (2280)	90" (2280)	90" (2280)	90" (2280)
Width inches (mm)	24" (600)	24" (600)	30" (750)	30" (750)	24" (600)	24" (600)	30" (750)	30" (750)
Depth inches (mm)	42" (1070)	48" (1200)	42" (1070)	48" (1200)	42" (1070)	48" (1200)	42" (1070)	48" (1200)
Door Type (Perforated)	Single front and split rear							
Weight Capacity (Static)	3750 lbs.							
Weight Capacity (Dynamic)	2250 lbs.							
Net Weight	257.9 lbs.	287.7 lbs.	313.1 lbs.	342.8 lbs.	294.3 lbs.	324.1 lbs.	360.5 lbs.	390.2 lbs.
Baying Configurations	600mm centers, 24" centers	600mm centers, 24" centers	750mm centers	750mm centers	600mm centers, 24" centers	600mm centers, 24" centers	750mm centers	750mm centers

TS IT Pro without Sidewalls

Part Number	9982.203	9982.207	9982.205	9982.209	9982.211	9982.215	9982.213	9982.217
RU Height	42U	42U	42U	42U	48U	48U	48U	48U
Height inches (mm)	79" (2012)	79" (2012)	79" (2012)	79" (2012)	90" (2280)	90" (2280)	90" (2280)	90" (2280)
Width inches (mm)	24" (600)	24" (600)	30" (750)	30" (750)	24" (600)	24" (600)	30" (750)	30" (750)
Depth inches (mm)	42" (1070)	48" (1200)	42" (1070)	48" (1200)	42" (1070)	48" (1200)	42" (1070)	48" (1200)
Door Type (Perforated)	Single front and split rear							
Weight Capacity (Static)	3750 lbs.							
Weight Capacity (Dynamic)	2250 lbs.							
Net Weight	205 lbs.	226 lbs.	260.1 lbs.	281.1 lbs.	232.6 lbs.	262.3 lbs.	298.7 lbs.	328.5 lbs.
Baying Configurations	600mm centers, 24" centers	600mm centers, 24" centers	750mm centers	750mm centers	600mm centers, 24" centers	600mm centers, 24" centers	750mm centers	750mm centers

Rittal North America LLC

Woodfield Corporate Center • 425 N. Martingale Road, Suite 400 • Schaumburg, IL • USA

1 Rittal Place • Urbana Ohio 43078 • USA

Phone: 937-399-0500 • Fax: 800-477-4003 • Toll-free: 800-477-4000

Email: rittal@rittal.us • Online: www.rittal.us

US543 ■ 3/21

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

