

Rittal – The System.

Faster – better – everywhere.

TS IT Pro Enclosures & Accessories

TS IT Pro with Side Panels

Part No.	RU Height	Height with Casters	Width	Depth	Door Type	Weight Capacity (Static)	Weight Capacity (Dynamic)	Net Weight of Each Rack	Color
9982.202	42 U	79" (2012 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	258 lb.	Black
9982.206	42 U	79" (2012 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	288 lb.	Black
9982.204	42 U	79" (2012 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	313 lb.	Black
9982.208	42 U	79" (2012 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	343 lb.	Black
9982.210	48 U	90" (2279 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	294 lb.	Black
9982.214	48 U	90" (2279 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	324 lb.	Black
9982.212	48 U	90" (2279 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	360 lb.	Black
9982.216	48 U	90" (2279 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	390 lb.	Black
9982.218	53 U	99" (2504 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	318 lb.	Black
9982.219	53 U	99" (2504 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	395 lb.	Black
9982.220	53 U	99" (2504 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	428 lb.	Black
9982.221	53 U	99" (2504 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	506 lb.	Black

TS IT Pro without Side Panels

Part No.	RU Height	Height with Casters	Width	Depth	Door Type	Weight Capacity (Static)	Weight Capacity (Dynamic)	Net Weight of Each Rack	Color
9982.203	42 U	79" (2012 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	205 lb.	Black
9982.207	42 U	79" (2012 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	226 lb.	Black
9982.205	42 U	79" (2012 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	260 lb.	Black
9982.209	42 U	79" (2012 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	281 lb.	Black
9982.211	48 U	90" (2279 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	233 lb.	Black
9982.215	48 U	90" (2279 mm)	24" (600 mm)	48" (1200mm)	Perforated front and rear	3750 lb.	2250 lb.	262 lb.	Black
9982.213	48 U	90" (2279 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	299 lb.	Black
9982.217	48 U	90" (2279 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	328 lb.	Black

TS IT Pro Shiploadable Enclosure with Side Panels

Part No.	RU Height	Height with Casters	Width	Depth	Door Type	Weight Capacity (Static)	Weight Capacity (Dynamic)	Net Weight of Each Rack	Color
9982.226	42 U	79" (2012 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	258 lb.	Black
9982.227	42 U	79" (2012 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	313 lb.	Black
9982.228	42 U	79" (2012 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	288 lb.	Black
9982.229	42 U	79" (2012 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	343 lb.	Black
9982.230	48 U	90" (2279 mm)	24" (600 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	294 lb.	Black
9982.231	48 U	90" (2279 mm)	30" (750 mm)	42" (1070 mm)	Perforated front and rear	3750 lb.	2250 lb.	361 lb.	Black
9982.232	48 U	90" (2279 mm)	24" (600 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	324 lb.	Black
9982.233	48 U	90" (2279 mm)	30" (750 mm)	48" (1200 mm)	Perforated front and rear	3750 lb.	2250 lb.	390 lb.	Black



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

TS IT Pro Cable Management Accessories

Model No.	Description	For Enclosure Height	For Enclosure Width	Unit of Issue	Color
9982.239	Vertical Cable Duct for TS IT Pro	42 U	750 mm	1	Black
9982.240	Vertical Cable Duct for TS IT Pro	48 U	750 mm	1	Black
9982.241	Vertical Cable Duct for TS IT Pro	53 U	750 mm	1	Black
9982.295	Cable Management Wall	42 U	-	2	Black
9982.296	Cable Management Wall	48 U	-	2	Black
9982.297	Cable Management Wall	53 U	-	2	Black
9982.272	Cable Management Fingers for TS IT Pro	42 U	-	1	Black
9982.273	Cable Management Fingers for TS IT Pro	48 U & 53 U	-	1	Black
9982.275	Front to Rear Cable Duct for TS IT Pro	-	750 mm	1	Black
9969.736	Horizontal Cable Management with hingeable/removeable cover Height 1 U	-	-	2	Black
9969.597	Horizontal Cable Management with hingeable/removeable cover Height 2 U	-	-	2	Black
9969.599	Quarter-turn Cable Managers for TS IT Pro 17" Fastener Strap	-	-	10	Black
9969.600	Quarter-turn Cable Managers for TS IT Pro Width 3" Depth 4.45" Collection Claw	-	-	10	Black
9961.779	Quarter-turn Cable Management D-ring for TS IT Pro Size 4.25" x 2"	-	-	10	Black
9961.780	Quarter-turn Cable Management D-ring for TS IT Pro Size 5" x 3.5"	-	-	10	Black
9982.270	Roof Mount Cable Manager for cable routing	-	600 mm	1	Black
9982.271	Roof Mount Cable Manager for cable routing	-	750 mm	1	Black
9982.238	Roof Mount Cable Manager End Plate	-	-	2	Black

TS IT Pro Rack Accessories

Model No.	Description	For Enclosure Height	For Enclosure Width	Kit	Color
9982.291	Anti-Tip Brackets for TS IT Pro	-	600 mm	1	Black
9982.292	Anti-Tip Brackets for TS IT Pro	-	750 mm	1	Black
9982.293	Bolt Down Bracket Kit for TS IT Pro	-	600 mm	1	Black
9982.294	Bolt Down Bracket Kit for TS IT Pro	-	750 mm	1	Black
9982.234	L & R Side Panels for TS IT Pro	42 U	1070 mm	1	Black
9982.235	L & R Side Panels for TS IT Pro	42 U	1200 mm	1	Black
9982.236	L & R Side Panels for TS IT Pro	48 U	1070 mm	1	Black
9982.237	L & R Side Panels for TS IT Pro	48 U	1200 mm	1	Black
9982.299	L & R Side Panels for TS IT Pro	53 U	1070 mm	1	Black
9982.300	L & R Side Panels for TS IT Pro	53 U	1200 mm	1	Black
9982.276	PDU Mount Brackets for TS IT Pro	-	750 mm	1	Black
9982.301	TS IT Pro Grounding Kit	-	-	1	Black
2090.000	1U M5 Cage Nut (12 sets)	-	-	-	Black
7094.130	M5 Screws (50/package)	-	-	-	Black

TS IT Pro Rack Handles and Lock Inserts

Model No.	Description	Version	Kit	Color
8611.360	Handles for TS IT Pro	Comfort handle for semi-cylinder inserts	1	Black
7720.801	Handles for TS IT Pro	3 digit combination security handle	1	Black
8611.200	Lock Inserts for TS IT Pro	Push-button, key lock with 2123 lock	1	-
8611.190	Lock Inserts for TS IT Pro	Push-button without Key Lock	1	-
8611.180	Lock Inserts for TS IT Pro	Lock Number 3524	1	-
8611.350	Handles for TS IT Pro	Comfort handle for round insert	1	Black
2469.000	Lock Inserts for TS IT Pro	Push button, key lock with 2123 lock	1	-
2468.000	Lock Inserts for TS IT Pro	Push Button without Key Lock	1	-
2467.000	Lock Inserts for TS IT Pro	Lock Number 3524 E	1	-

TS IT Pro Airflow Management Accessories

Model No.	Description	For Enclosure Height	For Enclosure Width	Kit	Color
9982.261	Foam Baffle for TS IT Pro *	42 U	600 mm	1	Black
9982.262	Foam Baffle for TS IT Pro *	48 U	600 mm	1	Black
9982.263	Foam Baffle for TS IT Pro *	53 U	600 mm	1	Black
9982.264	Brush Baffle for TS IT Pro	42 U	750 mm	2	Black
9982.265	Brush Baffle for TS IT Pro	48 U	750 mm	2	Black
9982.266	Brush Baffle for TS IT Pro	53 U	750 mm	2	Black
9982.267	Top Metal Baffle for TS IT Pro	-	600 mm	1	Black
9982.268	Top Metal Baffle for TS IT Pro	-	750 mm	1	Black

*Foam baffles only for bayed racks without side panels.

Rittal North America LLC

Woodfield Corporate Center
425 North Martingale Road, Suite 400
Schaumburg, Illinois 60173 • USA
Phone: 937-399-0500 • Toll-free: 800-477-4000
Email: rittal@rittal.us • Online: www.rittal.com

UST789-OS-TR ■ 6/23

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

