

The New 3-Part AX Wall-Mounted Enclosure – Less Complexity, More Flexibility



Robust Design, Versatile Use

The new 3-Part AX wall-mounted enclosure make system integration easy with peak **flexibility, accessibility,** and **time-saving benefits.** Great for networking gear, battery backups, servers, and more, it opens up possibilities for several applications where space is limited.

Conversion Assistant – New 3-Part AX Wall-Mounted Enclosure

Model No.	Article designation	Dimension [mm]			U	Model No. new	Article designation new	Note
		Width	Height	Depth				
2253.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	212	473	3	–	–	This enclosure is omitted without replacement.
2243.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	212	373	3	–	–	This enclosure is omitted without replacement.
2256.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	345	473	6	2260.640	AX wall-mounted enclosure, 3-part, 6 U	The mounting panel is omitted from the scope of supply. If required, it can be replaced by a AX 3-Part mounting panel.
2246.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	345	373	6	2260.630	AX wall-mounted enclosure, 3-part, 6 U	
2259.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	478	473	9	2260.940	AX wall-mounted enclosure, 3-part, 9 U	
2249.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	478	373	9	2260.930	AX wall-mounted enclosure, 3-part, 9 U	
2262.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	612	473	12	2261.240	AX wall-mounted enclosure, 3-part, 12 U	The mounting panel is omitted from the scope of supply. If required, it can be replaced by a AX 3-Part mounting panel.
2252.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	612	373	12	2261.230	AX wall-mounted enclosure, 3-part, 12 U	
2265.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	746	473	15	2261.540	AX wall-mounted enclosure, 3-part, 15 U	This enclosure is omitted without replacement.
2255.605	EL wall-mounted enclosure, 3-part with mounting panel and mounting angles, static installation	600	746	373	15	–	–	

Conversion Assistant – New 3-Part AX Wall-Mounted Enclosure

Model No.	Article designation	Dimension [mm]			U	Model No. new	Article designation new	Note
		Width	Height	Depth				
2261.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	1012	373	21	2262.130	AX wall-mounted enclosure, 3-part, 21 U	The mounting plate is omitted from the scope of supply. If required, it can be replaced by a KX mounting plate.
2271.605	EL wall-mounted enclosure, 3-part with mounting plate and mounting angles, static installation	600	1012	473	21	2262.140	AX wall-mounted enclosure, 3-part, 21 U	
7706.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	345	473	6	2260.640	AX wall-mounted enclosure, 3-part, 6 U	The C rails are omitted from the scope of supply. If required, they can be replaced by the 30/15 C rail or, depending on the application, by support strips or 14 x 39 mm VX punched sections with mounting flange from the system accessories.
7709.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	478	473	9	2260.940	AX wall-mounted enclosure, 3-part, 9 U	
7712.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	612	473	12	2261.240	AX wall-mounted enclosure, 3-part, 12 U	
7715.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	746	473	15	2261.540	AX wall-mounted enclosure, 3-part, 15 U	
7721.135	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	1012	473	21	2262.140	AX wall-mounted enclosure, 3-part, 21 U	
7709.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	478	673	9	2260.965	AX wall-mounted enclosure, 3-part, 9 U	C rails and grounding rail are omitted from the scope of supply. These components can be ordered as required from our range of system accessories.
7709.735	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	478	573	9	2260.955	AX wall-mounted enclosure, 3-part, 9 U	
7715.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	746	673	15	2261.565	AX wall-mounted enclosure, 3-part, 15 U	
7715.735	EL wall-mounted enclosure, 3-part with punched rails and mounting angles, depth-adjustable	600	746	573	15	2261.555	AX wall-mounted enclosure, 3-part, 15 U	
7721.535	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	1012	673	21	2262.165	AX wall-mounted enclosure, 3-part, 21 U	
7721.735	EL wall-mounted enclosure, 3-part, preassembled with mounting angles, depth-adjustable	600	1012	573	21	2262.155	AX wall-mounted enclosure, 3-part, 21 U	

Matching Model Numbers for Accessories for 3-Part AX Wall-Mounted Enclosure

Gland plates for 3-part AX wall-mounted enclosure	
Model No.	Designation
2260.060	With brush strip
2260.070	With metric knockouts

AX 3-part mounting panel	
Model No.	Suitable for enclosure height x width (mm)
1560.600	345x600 (6U)
1560.900	478x600 (9U)
1561.200	612x600 (12U)
1561.500	756x600 (15U)
1562.100	1012x600 (21U)

VX punched section with mounting flange, 14 x 39 mm	
Model No.	For installation in
8619.700	437 mm deep enclosure
8619.710	573 mm deep enclosure
8619.720	673 mm deep enclosure or in the width of the wall section

Support strip	
Model No.	For installation in
4594.000	437 mm deep enclosure
4309.000	573 mm deep enclosure
4596.000	673 mm deep enclosure or in the width of the wall section

Grounding rail, horizontal	
Model No.	For installation in
7113.000	The width of the wall section

30/15 C rail in accordance with EN 60715		
Model No.	Length [mm]	Note
4943.000	455	Depending on the installation, the rails must be cut to length in the width or depth.
4944.000	555	
4945.000	755	
4946.000	955	
4947.000	1155	

Blue e+ outlet filter		
Model No.	Suitable for	Color
3238.300	Center part of the wall-mounted enclosure	RAL 7035
3238.308	Center part of the wall-mounted enclosure	RAL 9005

You can find the contact details of all Rittal companies throughout the world here.



www.rittal.com/contact