




E-Box EB



- 1** For EB 1557.500/
EB 1578.500/EB 1579.500
two locks
- 2** For EB 1551.500
and EB 1553.500
- 3** Only for EB 1579.500




- 4** View A



- 5** For 125 mm wide mounting
plates, attachment is in the
centre only

View A
for
wall mounting



- 6** Knockout 2 mm
recessed

- B1 = Overall width
- B2 = Door width
- B3 = Clearance width
- H1 = Overall height
- H2 = Door height
- H3 = Clearance height
- T1 = Overall depth
- T2 = Clearance depth
available for installation
- F1 = Mounting plate width
- F2 = Outer edge to centre
mounting holes
- G1 = Mounting plate height

Model No. EB	Width dimensions mm			Height dimensions mm			Depth dimensions mm		Mounting plate dimensions mm		
	B1	B2	B3	H1	H2	H3	T1	T2	F1	F2	G1
1551.500	150	148	132	150	148	132	80	65	125	62.5	135
1545.500	150	148	132	300	298	282	80	65	125	62.5	285
1546.500	200	198	182	200	198	182	80	65	175	50	185
1552.500	200	198	182	300	298	282	80	65	175	50	285
1547.500	200	198	182	400	398	382	80	65	175	50	385
1553.500	150	148	132	150	148	132	120	105	125	62.5	135
1548.500	150	148	132	300	298	282	120	105	125	62.5	285
1549.500	200	198	182	200	198	182	120	105	175	50	185
1554.500	200	198	182	300	298	282	120	105	175	50	285
1550.500	200	198	182	400	398	382	120	105	175	50	385
1555.500	300	298	282	300	298	282	120	105	275	50	285
1556.500	300	298	282	400	398	382	120	105	275	50	385
1557.500	200	198	182	500	498	482	120	105	175	50	485
1577.500	300	298	282	400	398	382	155	140	275	50	385
1578.500	300	298	282	600	598	582	155	140	275	50	585
1579.500	300	298	282	800	798	782	155	140	275	50	785