

### Wentylatory filtrujące TopTherm

Nr kat. SK	Wymiary wykroju montażowego mm		Wymiary otworów	
	B2	H2	$\square$ Ø mm	F mm
3237.100	92	92	3,5	100,5
3237.600				
3237.110				
3237.124				
3238.100	124	124	3,5	132,5
3238.500				
3238.600				
3238.110				
3238.124	177	177	4,5	185
3239.100				
3239.500				
3239.600				
3239.110	224	224	4,5	234
3239.124				
3240.100				
3240.500				
3240.600	292	292	4,5	302
3240.110				
3240.124				
3241.100				
3241.500	292	292	4,5	302
3241.600				
3241.110				
3241.124				
3243.100	292	292	4,5	302
3243.500				
3243.600				
3243.110				
3244.100	292	292	4,5	302
3244.500				
3244.600				
3244.110				
3244.140	292	292	4,5	302
3245.500				
3245.600				
3245.510				

