



IEC	5 x 40 x 1 - 10 x 63 x 1 (Cu) 20 Nm		
UL	5 x 40 x 1 - 10 x 63 x 1 75° C copper 195 lb-in	-	-
	50 mm	50 mm	55 mm

1 SV Anschlussblock 1600A, 1-polig
60 mm Schienenmittenabstand

1 SV Connection block 1600A, 1-pole
60 mm busbar centre distance

1 Bloc de raccordement SV 1600A, 1-pôle
60 mm d'écartement entre les axes des barres

Article No.	SV9342.321	
Suitable for use on a circuit capable of delivering not more than SCCR symmetrical amperes [kA]	Maximum voltage AC [V]	Maximum condition when protected by
65	600	Class L 1600A Fuses
	480	Circuit breaker (UL category DIVQ/7) rated up to 1200A, having an interrupting rating not less than 65kA symmetrical amperes

Dok.-Nr. / No. of doc.: A4168105SV
Versandbeutel-Nr. / No. of accessory bag : -

Made in XXXXX
Lieferanten-Nr. / No. of supplier :

RITTAL GmbH & Co. KG, Auf dem Stuetzelberg, 35745 Herborn
RITTAL Limited, Braithwell Way, Hellaby, Rotherham, S66 8QY, UK

