



SV
9341.050

Raum für Verpackungsdatum
Area for date of packing
(MMJJTT / MMYYYDD)

4 Sammelschienenhalter PLS 800
60 mm Schienenmittenabstand

4 Busbar support PLS 800
60 mm busbar centre distance

4 Supports de jeux de barres PLS 800
60 mm d'écartement entre les axes des barres

Article No.	SV9341.050		
Suitable for use on a circuit capable of delivering not more than SCCR symmetrical amperes [kA]	Maximum voltage AC [V]	Maximum condition when protected by	Spacing between supports [mm]
65	600	Class J 600A Fuses	150
	480	Circuit breaker (UL category DIVQ/7) rated up to 600A, having an interrupting rating not less than 65kA symmetrical amperes	150
50	600	Class L 800A Fuses	250
	600	Circuit breaker (UL category DIVQ/7) rated up to 600A, having an interrupting rating not less than 50kA symmetrical amperes	250
22	600	-	200
14	600	-	500

Dok.-Nr. / No. of doc.: A3637506SV
Versandbeutel-Nr. / No. of accessory bag: -

Made in XXXXX
Lieferanten-Nr. / No. of supplier:

RITTAL GmbH & Co. KG, Auf dem Stuetzelberg, 35745 Herborn
RITTAL Limited, Braithwell Way, Hellaby, Rotherham, S66 8QY, UK

