

RITTAL GmbH & Co. KG

AUF DEM STÜTZELBERG  
D-35745 Herborn  
  
<http://www.rittal.de>





MODEL	:	SK3336.405	REFRIGERANT	:	R513A	
DRAWING NUMBER	:	FP25116	-	VOLTAGE	:	400V 3 50Hz / 460V 3 60Hz [TT]
PRODUCT FAMILY	:	KRAE	081	:		
VARIANT/SPECIAL	:	V395	:			
			CUSTOMER	:		
			REFERENCE	:		

CREATED THE	:	01/09/2025	BY	MT1	
CHANGED ON THE	:		BY		NUMBER OF PAGES : 5

PAGE OVERVIEW

2LP8_PAGKEL			
PAGE	DESIGNATION	DATE REVISION	REVISOR
/1	COVER		
/2	PAGE OVERVIEW		
/3	REFRIGERANT CIRCUIT		
/4	HYDRAULIC CIRCUIT		
/5	BILL OF MATERIAL		





BILL OF MATERIAL



2LP8\_RICKEL\_FLUID

DESIGNATION	AMOUNT	ARTICLE NUMBER	DESIGNATION 1	DESIGNATION 2	MANUFACTURER	INTERNAL NO	PAGE / PATH
AV	1	VAS22	REFTUBE ANTIV 22mm STSTEEL PN35		VERCO	900450	/3.6
BA	1	682182001	DISCHARGE VALVE 90° 1" BRONZE	2-10 bar	ACQUATICA SRL	910497	/4.6
BC	1	J000458	HEX MICRO CN 25 10 32 L25 25 630 877 2	598x876	CLIMETAL	926221	/3.3
FI	1	023Z4571	FILTER DEIDR DANFOSS DML084	SALD 12mm R410A, R407C, R134a, R404A	DANFOSS	916264	/3.0
-LE	1	EURP006F7001/0	ELECTRIC LEVEL EUROSITCH P006 2 LEV.	BLU-1° LIV MARR-2°LIV NERO-3°COMUNE	EUROSITCH	918289	/4.1
M1	1	MLZ038T4LC9A	COMP SCROLL DANFOSS MLZ038T4LC9A	400 3 50,460 3 60 80,95cm3 R513A cURu 121L8645	DANFOSS	928877	/3.6
M2	1	A4D450-A014-10	FAN AXIAL EBM A4D450-AO14-10	450mm 400 3 50, 480 3 60 +GRIGLIA 106FG0702	EBMPAPST SRL	916116	/3.3
M3	1	3HM05P15TBRQQVXF	PUMP LOWARA 3HM05P15TBRQQVXF EPL 50/60	400 3 50, 400-460 3 60 SEALS BELLOW VERSION	LOWARA SRL	927400	/4.4
MN	1	FMTPG351014LF	MANOMETER DIPPED GLICERINE FIMET 0-10bar	D.63 1/4" PG351014LF	FIMET	900442	/4.5
-PA	1	715556	PRESSHP PSAH FIX 21-16	ALCO PS3-W6S	ALCO	909394	/3.6
-PB	1	EBAL1702E	PRESS LP FIX 0,5-2	ALCO PS3-A1S	ALCO	902408	/3.6
PHE	1	B80ASHx18/1P-SC-M	SCAMBIATORE A PIASTRE SWEP B80ASHx18/1P-SC-M	SALDOBRASATO AL RAME 12.8+22U+2x1 1/4"&28U	SWEP INTERNATIONAL AB	928879	/3.3
-PV	1	060-509666	PRESSHP PSAH VAR 8-32 RIARMO AUTOMATICO	DANFOSS KP5	DANFOSS	902393	/3.2
SG	1	VBK502	VALV REF SOL RSG VBK502	1/2" (12mm) 24Vdc	REGEL-UND STEUERGERÄTE GMBH	917296	/3.3
SLG	1	1078N/M12S	VALV REF SOL CASTEL 1078N/M12S	12mm , UL, WITHOUT COIL	CASTEL SRL	927729	/3.1
SV	1	1032404	SHUTTER VALVE M1/2"	PN16 PLUG+HOSE FITTINGS BRASS	OVENTROP SRL	925478	/4.0
TP	1	401 / 2.1/2"	CAP MALE 2"1/2 PE L.D. YELLOW	OLEODINAMICA PASINI 401 / 2.1/2"	OLEODINAMICA PASINI	927149	/4.2
VA	1	J000416_TYPE1	CAR TANK 520x620x210 PE 50L	4x1"1/4+2x1"+1x1/2" LE, BRASS SLEEVES	VERZELLES SRL	926304	/4.0
VT	1	067N5302	VALVEXP TERMOST DANFOSS R513A TGE 10-8	067N5302 SALD 12-22-6 R513A	DANFOSS	928878	/3.1
-Y1	1	9320/RD2	VALV-COIL GAS CASTEL 9320/RD2	24VDC-50/60Hz, UL, 8W, WITH CONNECTOR 9150/R02	CASTEL SRL	927732	/3.1

4