

Rittal – The System.

Faster – better – worldwide.

➤ **Make IT easy**
Your conversion aid: From TS8 to TS IT



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

Product range TS8

TS8 Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (round grommets)	180° hinges		Handle for individual lock			Catalog 33 page
		RAL 7035 Light Grey	Sand Texture Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	Base/plinth	
								Viewing door	Solid	Perforated	Solid	Perforated							
TS8 Server Enclosure Full Front and Split Rear Perforated Doors																			
9963.702	TS8 Server enclosure	■	-	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.716	TS8 Server Enclosure	■	-	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.703	TS8 Server Enclosure	-	■	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.717	TS8 Server Enclosure	-	■	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.704	TS8 Server Enclosure	■	-	700	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.706	TS8 Server Enclosure	■	-	800	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.718	TS8 Server Enclosure	■	-	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.720	TS8 Server Enclosure	■	-	800	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.705	TS8 Server Enclosure	-	■	700	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.707	TS8 Server Enclosure	-	■	800	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	134
9963.719	TS8 Server Enclosure	-	■	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.721	TS8 Server Enclosure	-	■	800	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.730	TS8 Server Enclosure	■	-	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.742	TS8 Server Enclosure	■	-	600	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.743	TS8 Server enclosure	-	■	600	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.732	TS8 Server Enclosure	■	-	700	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.734	TS8 Server Enclosure	■	-	800	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.744	TS8 Server Enclosure	■	-	800	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.733	TS8 Server Enclosure	-	■	700	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.745	TS8 Server Enclosure	-	■	800	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	136
9963.731	TS8 Server Enclosure	-	■	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	135
9963.735	TS8 Server Enclosure	-	■	800	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	136

TS8 Server Enclosure Full Front and Split Rear Perforated Doors																			
9963.708	TS8 Server enclosure	■	-	600	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	134
9963.722	TS8 Server Enclosure	■	-	600	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.709	TS8 Server Enclosure	-	■	600	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	134
9963.723	TS8 Server Enclosure	-	■	600	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.710	TS8 Server Enclosure	■	-	700	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	134
9963.712	TS8 Server Enclosure	■	-	800	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.724	TS8 Server Enclosure	■	-	700	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.726	TS8 Server Enclosure	■	-	800	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.711	TS8 Server Enclosure	-	■	700	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.713	TS8 Server Enclosure	-	■	800	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.725	TS8 Server Enclosure	-	■	700	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.727	TS8 Server Enclosure	-	■	800	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	135
9963.736	TS8 Server Enclosure	■	-	600	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.746	TS8 Server Enclosure	■	-	600	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.747	TS8 Server enclosure	-	■	600	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.738	TS8 Server Enclosure	■	-	700	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.740	TS8 Server Enclosure	■	-	800	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.748	TS8 Server Enclosure	■	-	800	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.739	TS8 Server Enclosure	-	■	700	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.749	TS8 Server Enclosure	-	■	800	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.737	TS8 Server Enclosure	-	■	600	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136
9963.741	TS8 Server Enclosure	-	■	800	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	136

Product range TS IT

TS IT Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (side entry with brush inserts)	180° hinges		Handle for individual lock		Base/plinth
		RAL 7035 Light Grey	RAL 9005 Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	
								Viewing door	Solid	Perforated	Solid	Perforated						
5508.110		■	-	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5508.210		-	■	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.110		■	-	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.210		-	■	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5510.110		■	-	600	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5510.210		-	■	600	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5511.110		■	-	800	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5511.210		-	■	800	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5523.210		-	■	600	2000	1050	47	-	-	■	-	■	■	■	■	■	■	-
5522.210		-	■	800	2000	1050	42	-	-	■	-	■	■	■	■	■	■	-
5513.110		■	-	600	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5513.210		-	■	600	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5514.110		■	-	800	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5514.210		-	■	800	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5515.110		■	-	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5515.210		-	■	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.110		■	-	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.210		-	■	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5523.210		-	■	600	2200	1050	47	-	-	■	-	■	■	■	■	■	■	-
5524.210		-	■	800	2200	1050	47	-	-	■	-	■	■	■	■	■	■	-

Product range TS8

TS8 Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (round grommets)	180° hinges		Handle for individual lock		Base/plinth	Catalog 33 page
		RAL 7035 Light Grey	Sand Texture Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear		
								Viewing door	Solid	Perforated	Solid	Perforated							
42U TS8 Server Enclosure - Full Front Door / Split Rear Doors, Slam latch on rear door																			
9969.818	42U TS8 Server Enclosure	■	-	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.832	42U TS8 Server Enclosure	■	-	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.819	42U TS8 Server Enclosure	-	■	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.833	42U TS8 Server Enclosure	-	■	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.820	42U TS8 Server Enclosure	■	-	700	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.822	42U TS8 Server Enclosure	■	-	800	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.834	42U TS8 Server Enclosure	■	-	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.836	42U TS8 Server Enclosure	■	-	800	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.821	42U TS8 Server Enclosure	-	■	700	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.823	42U TS8 Server Enclosure	-	■	800	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.835	42U TS8 Server Enclosure	-	■	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.837	42U TS8 Server Enclosure	-	■	800	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.846	42U TS8 Server Enclosure	■	-	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.908	42U TS8 Server Enclosure	■	-	600	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.909	42U TS8 Server Enclosure	-	■	600	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.848	42U TS8 Server Enclosure	■	-	700	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.850	42U TS8 Server Enclosure	■	-	800	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.910	42U TS8 Server Enclosure	■	-	800	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.849	42U TS8 Server Enclosure	-	■	700	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.911	42U TS8 Server Enclosure	-	■	800	2000	1200	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.847	42U TS8 Server Enclosure	-	■	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.851	42U TS8 Server Enclosure	-	■	800	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-

47U TS8 Server Enclosure - Full Front Door / Split Rear Doors																			
9969.824	47U TS8 Server Enclosure	■	-	600	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.838	47U TS8 Server Enclosure	■	-	600	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.825	47U TS8 Server Enclosure	-	■	600	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.839	47U TS8 Server Enclosure	-	■	600	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.826	47U TS8 Server Enclosure	■	-	700	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.828	47U TS8 Server Enclosure	■	-	800	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.840	47U TS8 Server Enclosure	■	-	700	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.842	47U TS8 Server Enclosure	■	-	800	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.827	47U TS8 Server Enclosure	-	■	700	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.829	47U TS8 Server Enclosure	-	■	800	2200	900	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.841	47U TS8 Server Enclosure	-	■	700	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.843	47U TS8 Server Enclosure	-	■	800	2200	1000	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.852	47U TS8 Server Enclosure	■	-	600	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.912	47U TS8 Server Enclosure	■	-	600	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.913	47U TS8 Server Enclosure	-	■	600	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.854	47U TS8 Server Enclosure	■	-	700	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.856	47U TS8 Server Enclosure	■	-	800	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.914	47U TS8 Server Enclosure	■	-	800	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.855	47U TS8 Server Enclosure	-	■	700	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.915	47U TS8 Server Enclosure	-	■	800	2200	1200	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.853	47U TS8 Server Enclosure	-	■	600	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-
9969.857	47U TS8 Server Enclosure	-	■	800	2200	1050	47	-	-	■	-	■	■	-	-	■	■	-	-

Product range TS IT

TS IT Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (side entry with brush inserts)	180° hinges		Handle for individual lock		Base/plinth
		RAL 7035 Light Grey	RAL 9005 Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	
								Viewing door	Solid	Perforated	Solid	Perforated						
5508.110		■	-	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5508.210		-	■	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.110		■	-	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.210		-	■	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5510.110		■	-	600	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5510.210		-	■	600	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5511.110		■	-	800	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5511.210		-	■	800	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5521.210		-	■	600	2000	1050	42	-	-	■	-	■	■	■	■	■	■	-
5522.210		-	■	800	2000	1050	42	-	-	■	-	■	■	■	■	■	■	-
5513.110		■	-	600	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5513.210		-	■	600	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5514.110		■	-	800	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5514.210		-	■	800	2000	1000	47	-	-	■	-	■	■	■	■	■	■	-
5515.110		■	-	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5515.210		-	■	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.110		■	-	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.210		-	■	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5523.210		-	■	600	2200	1050	47	-	-	■	-	■	■	■	■	■	■	-
5524.210		-	■	800	2200	1050	47	-	-	■	-	■	■	■	■	■	■	-

Product range TS8

TS8 Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (round grommets)	180° hinges		Handle for individual lock			Catalog 33 page
		RAL 7035 Light Grey	Sand Texture Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	Base/plinth	
								Viewing door	Solid	Perforated	Solid	Perforated							
24U TS8 Server Enclosure - Full Front Door / Split Rear Doors																			
9969.816	24U TS8 Server Enclosure	■	-	600	1200	900	24	-	-	■	-	■	■	-	-	■	■	-	-
9969.830	24U TS8 Server Enclosure	■	-	600	1200	1000	24	-	-	■	-	■	■	-	-	■	■	-	-
9969.844	24U TS8 Server Enclosure	■	-	600	1200	1050	24	-	-	■	-	■	■	-	-	■	■	-	-
9969.817	24U TS8 Server Enclosure	-	■	600	1200	900	24	-	-	■	-	■	■	-	-	■	■	-	-
9969.831	24U TS8 Server Enclosure	-	■	600	1200	1000	24	-	-	■	-	■	■	-	-	■	■	-	-
9969.845	24U TS8 Server Enclosure	-	■	600	1200	1050	24	-	-	■	-	■	■	-	-	■	■	-	-

42U TS8 Server Enclosure - Full Front and Rear Perforated Doors																			
9969.808	42U TS8 Server Enclosure	■	-	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.810	42U TS8 Server Enclosure	■	-	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.809	42U TS8 Server Enclosure	-	■	600	2000	900	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.811	42U TS8 Server Enclosure	-	■	600	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.812	42U TS8 Server Enclosure	■	-	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.813	42U TS8 Server Enclosure	-	■	700	2000	1000	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.814	42U TS8 Server Enclosure	■	-	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-
9969.815	42U TS8 Server Enclosure	-	■	600	2000	1050	42	-	-	■	-	■	■	-	-	■	■	-	-

TS8 Network Enclosure - Vented Viewing Door / Split Rear Doors																			
9969.874	TS8 Network Enclosure	■	-	600	1200	600	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.858	TS8 Network Enclosure	■	-	600	1200	800	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.860	TS8 Network Enclosure	■	-	800	1200	800	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.875	TS8 Network Enclosure	-	■	600	1200	600	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.859	TS8 Network Enclosure	-	■	600	1200	800	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.861	TS8 Network Enclosure	-	■	800	1200	800	24	■	-	■	-	■	■	-	-	■	■	-	128
9969.862	TS8 Network Enclosure	■	-	600	2000	800	42	■	-	■	-	■	■	-	-	■	■	-	129
9969.863	TS8 Network Enclosure	-	■	600	2000	800	42	■	-	■	-	■	■	-	-	■	■	-	129
9969.864	TS8 Network Enclosure	■	-	800	2000	800	42	■	-	■	-	■	■	-	-	■	■	-	129
9969.865	TS8 Network Enclosure	-	■	800	2000	800	42	■	-	■	-	■	■	-	-	■	■	-	129
9969.866	TS8 Network Enclosure	■	-	600	2200	800	47	■	-	■	-	■	■	-	-	■	■	-	129
9969.867	TS8 Network Enclosure	-	■	600	2200	800	47	■	-	■	-	■	■	-	-	■	■	-	129
9969.868	TS8 Network Enclosure	■	-	800	2200	800	47	■	-	■	-	■	■	-	-	■	■	-	129
9969.869	TS8 Network Enclosure	-	■	800	2200	800	47	■	-	■	-	■	■	-	-	■	■	-	129

TS LCP Ready Cabinet																			
9971.034	LCP Ready	■	-	600	2000	1000	42	■	-	-	■	-	■	-	-	■	■	-	140
9962.166	LCP Ready	-	■	600	2000	1000	42	■	-	-	■	-	■	-	-	■	■	-	140
9971.036	LCP Ready	■	-	800	2000	1000	42	■	-	-	■	-	■	-	-	■	■	-	140
9962.168	LCP Ready	-	■	800	2000	1000	42	■	-	-	■	-	■	-	-	■	■	-	140
9971.035	LCP Ready	■	-	600	2000	1200	42	■	-	-	■	-	■	-	-	■	■	-	140
9962.167	LCP Ready	-	■	600	2000	1200	42	■	-	-	■	-	■	-	-	■	■	-	140
9971.037	LCP Ready	■	-	800	2000	1200	42	■	-	-	■	-	■	-	-	■	■	-	140
9962.169	LCP Ready	-	■	800	2000	1200	42	■	-	-	■	-	■	-	-	■	■	-	140

Product range TS IT

TS IT Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (side entry with brush inserts)	180° hinges		Handle for individual lock		Base/plinth
		RAL 7035 Light Grey	RAL 9005 Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	
								Viewing door	Solid	Perforated	Solid	Perforated						
5504.110		■	-	800	1200	1000	24	-	-	■	-	■	■	■	■	■	■	-
5504.210		-	■	800	1200	1000	24	-	-	■	-	■	■	■	■	■	■	-

5508.110		■	-	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5508.210		-	■	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.110		■	-	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.210		-	■	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5510.110		■	-	600	2000	1200	42	-	-	■	-	■	■	■	■	■	■	-
5521.210		-	■	600	2000	1050	42	-	-	■	-	■	■	■	■	■	■	-

5504.110		■	-	800	1200	1000	24	-	-	■	-	■	■	■	■	■	■	-
5504.210		-	■	800	1200	1000	24	-	-	■	-	■	■	■	■	■	■	-
5508.110		■	-	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5508.210		-	■	600	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.110		■	-	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5509.210		-	■	800	2000	1000	42	-	-	■	-	■	■	■	■	■	■	-
5515.110		■	-	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5515.210		-	■	600	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.110		■	-	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-
5516.210		-	■	800	2200	1200	47	-	-	■	-	■	■	■	■	■	■	-

5508.120		■	-	600	2000	1000	42	■	-	-	■	-	■	■	■	■	■	-
5508.220		-	■	600	2000	1000	42	■	-	-	■	-	■	■	■	■	■	-
5509.120		■	-	800	2000	1000	42	■	-	-	■	-	■	■	■	■	■	-
5509.220		-	■	800	2000	1000	42	■	-	-	■	-	■	■	■	■	■	-
5510.120		■	-	600	2000	1200	42	■	-	-	■	-	■	■	■	■	■	-
5510.220		-	■	600	2000	1200	42	■	-	-	■	-	■	■	■	■	■	-
5511.120		■	-	800	2000	1200	42	■	-	-	■	-	■	■	■	■	■	-
5511.220		-	■	800	2000	1200	42	■	-	-	■	-	■	■	■	■	■	-

Product range TS IT – No Current TS8 equivalent

TS IT Part No.	Design	Color		Dimensions inches (mm)				Doors					Roof for cable entry, rear (side entry with brush inserts)	180° hinges		Handle for individual lock		Base/plinth
		RAL 7035 Light Grey	RAL 9005 Black	W	H	D	U	Front			Rear			Front	Rear	Front	Rear	
								Viewing door	Solid	Perforated	Solid	Perforated						
5503.120		■	–	800	1200	800	24	■	–	–	■	–	■	■	■	■	–	
5503.220		–	■	800	1200	800	24	■	–	–	■	–	■	■	■	■	–	
5504.120		■	–	800	1200	1000	24	■	–	–	■	–	■	■	■	■	–	
5504.220		–	■	800	1200	1000	24	■	–	–	■	–	■	■	■	■	–	
5505.120		■	–	800	1800	800	38	■	–	–	■	–	■	■	■	■	–	
5505.220		–	■	800	1800	800	38	■	–	–	■	–	■	■	■	■	–	
5506.120		■	–	800	2000	600	42	■	–	–	■	–	■	■	■	■	–	
5506.220		–	■	800	2000	600	42	■	–	–	■	–	■	■	■	■	–	
5507.120		■	–	800	2000	800	42	■	–	–	■	–	■	■	■	■	–	
5507.220		–	■	800	2000	800	42	■	–	–	■	–	■	■	■	■	–	
5512.220		–	■	800	2200	800	47	■	–	–	■	–	■	■	■	■	–	

Accessory Range TS8 – TS IT

TS8 Part No.	Description	TS IT Part No.	Description
Walls			
Side panels			
9967.470	Split SW 2000H x 800D (Grey)	5501.020	Side panel divided, 79 x 32" (2000 x 800 mm), RAL 7035
9967.460	Split SW 2000H x 800D (Black)	5501.025	Side panel divided, 79 x 32" (2000 x 800 mm), RAL 9005
9967.472	Split SW 2000H x 1000D (Grey)	5501.030	Side panel divided, 79 x 40" (2000 x 1000 mm), RAL 7035
9967.462	Split SW 2000H x 1000D (Black)	5501.035	Side panel divided, 79 x 40" (2000 x 1000 mm), RAL 9005
9967.474	Split SW 2000H x 1200D (Grey)	5501.040	Side panel divided, 79 x 48" (2000 x 1200 mm), RAL 7035
9967.464	Split SW 2000H x 1200D (Black)	5501.045	Side panel divided, 79 x 48" (2000 x 1200 mm), RAL 9005
9967.475	Split SW 2200H x 800D (Grey)	5501.050	Side panel divided, 87 x 32" (2200 x 800 mm), RAL 7035
9967.465	Split SW 2200H x 800D (Black)	5501.055	Side panel divided, 87 x 32" (2200 x 800 mm), RAL 9005
9967.477	Split SW 2200H x 1000D (Grey)	5501.060	Side panel divided, 87 x 40" (2200 x 1000 mm), RAL 7035
9967.467	Split SW 2200H x 1000D (Black)	5501.065	Side panel divided, 87 x 40" (2200 x 1000 mm), RAL 9005
9967.479	Split SW 2200H x 1200D (Grey)	5501.070	Side panel divided, 87 x 48" (2200 x 1200 mm), RAL 7035
9967.469	Split SW 2200H x 1200D (Black)	5501.075	Side panel divided, 87 x 48" (2200 x 1200 mm), RAL 9005
9967.463	Split SW 2000H x 1050D (Black)	5501.095	Side panel divided, 79 x 42" (2000 x 1050 mm), RAL 9005
9967.468	Split SW 2200H x 1050D (Black)	5501.105	Side panel divided, 87 x 42" (2200 x 1050 mm), RAL 9005
9967.471	Split SW 2000H x 900D (Grey)	N/A	N/A
9967.461	Split SW 2000H x 900D (Black)	N/A	N/A
9967.473	Split SW 2000H x 1050D (Grey)	N/A	N/A
9967.476	Split SW 2200H x 900D (Grey)	N/A	N/A
9967.466	Split SW 2200H x 900D (Black)	N/A	N/A
9967.478	Split SW 2200H x 1050D (Grey)	N/A	N/A

Accessory Range TS8 – TS IT

TS8 Part No.	Description	TS IT Part No.	Description
Base			
4611.000	Twin Caster, 88 lbs static load per, Ground Clearance 2"	6148.000	Twin Caster, 165 lbs static load per, Ground Clearance 3"
9967.480	Complete Caster (600W-Black)	9968.751	Caster kit
9967.483	Complete Caster (600W-Grey)	9968.751	Caster kit
9967.481	Complete Caster (700W-Black)	9968.751	Caster kit
9967.484	Complete Caster (700W-Grey)	9968.751	Caster kit
9967.482	Complete Caster (800W-Black)	9968.751	Caster kit
9967.485	Complete Caster (800W-Grey)	9968.751	Caster kit

Interior installation

Component Shelves/Slides			
7119.250	2U Component Shelf 250D	5501.615	19", 2 U, Component shelf, 55 lbs. (25kg), 250 mm deep
7143.035	19" Component Shelf 110# (300D)	5501.625	19", 2 U, Component shelf, 55 lbs. (25kg), 400 mm deep
7119.400	2U Component Shelf 400D	5501.625	19", 2 U, Component shelf, 55 lbs. (25kg), 400 mm deep
7148.035	2U Component Shelf 300D w/telescopic slides	5501.625	19", 2 U, Component shelf, 55 lbs. (25kg), 400 mm deep
7144.035	19" Component Shelf 110# (400D)	5501.655	19", ½ U, Component shelf, 110 lbs. (50kg), 400-600 mm deep
7145.035	19" Component Shelf 110# (500D)	5501.655	19", ½ U, Component shelf, 110 lbs. (50kg), 400-600 mm deep
7063.858	Mounting Kit, 390-590, 110lbs.	5501.655	19", ½ U, Component shelf, 110 lbs. (50kg), 400-600 mm deep
7063.710	1/2U Component Shelf (400-600)	5501.665	19", ½ U, Component shelf, 110 lbs. (50kg), 600-900 mm deep
7145.635	19" Component Shelf 110# (600D)	5501.665	19", ½ U, Component shelf, 110 lbs. (50kg), 600-900 mm deep
7145.735	19" Component Shelf 110# (700D)	5501.665	19", ½ U, Component shelf, 110 lbs. (50kg), 600-900 mm deep
7063.860	Mounting Kit, 590-790, 110lbs.	5501.665	19", ½ U, Component shelf, 110 lbs. (50kg), 600-900 mm deep
7051.000	Telescopic slide 300D, 110lbs.	5501.675	19", 1 U, Component shelf, Pull Out, 110 lbs. (50kg), 400-600 mm deep
7061.000	Telescopic slide 400D, 110lbs.	5501.675	19", 1 U, Component shelf, Pull Out, 110 lbs. (50kg), 400-600 mm deep
7081.000	Telescopic slide 500D, 110lbs.	5501.675	19", 1 U, Component shelf, Pull Out, 110 lbs. (50kg), 400-600 mm deep
7063.720	1/2U Component Shelf (600-900)	5501.685	19", 1 U, Component shelf, Pull Out, 110 lbs. (50kg), 600-900 mm deep
7161.000	Telescopic slide 600D, 110lbs.	5501.685	19", 1 U, Component shelf, Pull Out, 110 lbs. (50kg), 600-900 mm deep
7063.895	19" Component Shelf 220# (500D)	5501.695	19", 1 U, Component shelf, 220 lbs. (100kg), 400-600 mm deep
7063.892	Mounting Kit, 490-710, 220lbs.	5501.695	19", 1 U, Component shelf, 220 lbs. (100kg), 400-600 mm deep
9968.421	Fixed Tool-less 19" Shelf (Grey)	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
9968.422	Fixed Tool-less 19" Shelf (Black)	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
7063.897	19" Component Shelf 220# (700D)	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
9968.556	19" HD Tool-less shelf Fixed Grey	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
9968.557	19" HD Tool-less shelf Fixed Black	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
9968.586	19" HD Tool-less shelf Telescopic Grey	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
9968.587	19" HD Tool-less shelf Telescopic Black	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
7063.890	Mounting Kit, 706.5-1006.5, 220lbs.	5501.705	19", 1 U, Component shelf, 220 lbs. (100kg), 600-900 mm deep
7064.000	Telescopic slide 400D, 220lbs.	5501.715	19", 1-½ U, Component shelf, Pull Out, 220 lbs. (100kg), 400-600 mm deep
7065.000	Telescopic slide 500D, 220lbs.	5501.715	19", 1-½ U, Component shelf, Pull Out, 220 lbs. (100kg), 400-600 mm deep
7066.000	Telescopic slide 600D, 220lbs.	5501.725	19", 1-½ U, Component shelf, Pull Out, 220 lbs. (100kg), 600-900 mm deep
7163.500	Cable Support, <600mm	N/A	N/A
7163.550	Cable Support, >600mm	N/A	N/A

Accessory Range TS8 – TS IT

TS8 Part No.	Description	TS IT Part No.	Description
Cable management			
Cable management			
9969.593	3.5" Wide Vertical Manager Kit	5502.105	Cable duct for enclosure height 79" (2000 mm)
9969.595	7.5" Wide Vertical Manager Kit	5502.105	Cable duct for enclosure height 79" (2000 mm)
9969.598	7.5" Wide Vertical Manager Kit, for 800W	5502.105	Cable duct for enclosure height 79" (2000 mm)
9963.600	18U Vertical Cable Manager	5502.115	Cable finger, 6 U
9970.254	Roofmount Cable Manager, 600W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.256	Roofmount Cable Manager, 700W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.258	Roofmount Cable Manager, 800W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.264	Roofmount Cable Mgr w/ladder prov, 600W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.266	Roofmount Cable Mgr w/ladder prov, 700W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.268	Roofmount Cable Mgr w/ladder prov, 800W, Black	5502.135	Roof system supports for cable routes, RAL 9005
9970.260	Roofmount end cover, black	5502.135	Roof system supports for cable routes, RAL 9005
9970.262	Roofmount manaaer LCP, black	5502.135	Roof system supports for cable routes, RAL 9005
9970.270	Roofmount end ladder installation brackets, black	5502.135	Roof system supports for cable routes, RAL 9005
7149.135	19" cable trough, 1U	5502.245	19", 1 U, Cable routing channel
7149.035	19" cable trough, 2U	5502.245	19", 1 U, Cable routing channel
7140.535	19" cable entry, 1U, grey	5502.255	19", 1 U, Cable entry panel
9967.361	19" cable entry, 1U, black	5502.255	19", 1 U, Cable entry panel
7150.535	19" cable entry, 2U, grey	5502.265	19", 2 U, Cable entry panel
9967.362	19" cable entry, 2U, black	5502.265	19", 2 U, Cable entry panel
9969.601	Cable Slack Spool	5502.405	Cable manager
9970.253	Roofmount Cable Manager, 600W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.255	Roofmount Cable Manager, 700W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.257	Roofmount Cable Manager, 800W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.263	Roofmount Cable Mgr w/ladder prov, 600W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.265	Roofmount Cable Mgr w/ladder prov, 700W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.267	Roofmount Cable Mgr w/ladder prov, 800W, Grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.259	Roofmount end cover, grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.261	Roofmount manager LCP, grey	7831.472	Roof system supports for cable routes, RAL 7035
9970.269	Roofmount end ladder installation brackets, grey	7831.472	Roof system supports for cable routes, RAL 7035
9969.594	3.5" Manager Cover	N/A	N/A
9969.596	7.5" Manager Cover	N/A	N/A
9967.365	Cable Trough, Tool-less	N/A	N/A
9967.364	Cable Management Bar, Tool-less	N/A	N/A
9970.271	Roofmount ladder rack	N/A	N/A

Accessory Range TS8 – TS IT

TS8 Part No.	Description	TS IT Part No.	Description
19" (482.6 mm) installation system			
19" (482.6 mm) installation			
9961.328	Air brush baffles, 42U x 600W	5501.805	Air baffle plate, 24 x 79" (600 x 2000 mm)
9978.352	Metal air baffles, 42U x 600W	5501.805	Air baffle plate, 24 x 79" (600 x 2000 mm)
9961.330	Air brush baffles, 42U x 800W	5501.815	Air baffle plate, 32 x 79" (800 x 2000 mm)
9978.354	Metal air baffles, 42U x 800W	5501.815	Air baffle plate, 32 x 79" (800 x 2000 mm)
9961.331	Air brush baffles, 47U x 600W	5501.825	Air baffle plate, 24 x 87" (600 x 2200 mm)
9978.355	Metal air baffles, 47U x 600W	5501.825	Air baffle plate, 24 x 87" (600 x 2200 mm)
9961.333	Air brush baffles, 47U x 800W	5501.835	Air baffle plate, 32 x 87" (800 x 2200 mm)
9978.357	Metal air baffles, 47U x 800W	5501.835	Air baffle plate, 32 x 87" (800 x 2200 mm)
9970.240	1U tool-less blanking panel, metal, grey	7151.005	1 U, Blanking panel, RAL 9005
7152.035	2U tool-less blanking panel, metal, grey smooth	7152.005	2 U, Blanking panel, RAL 9005
9970.241	3U tool-less blanking panel, metal, grey	7153.005	3 U, Blanking panel, RAL 9005
7153.035	3U tool-less blanking panel, metal, grey smooth	7153.005	3 U, Blanking panel, RAL 9005
7156.035	6U tool-less blanking panel, metal, grey smooth	7156.005	6 U, Blanking panel, RAL 9005
9971.066	Button Mount Bracket	N/A	N/A
9961.329	Air brush baffles, 42U x 700W	N/A	N/A
9961.332	Air brush baffles, 47U x 700W	N/A	N/A
9961.334	Brush Ring	N/A	N/A
9961.326	Snap Ring	N/A	N/A
9978.353	Metal air baffles, 42U x 700W	N/A	N/A
9978.356	Metal air baffles, 47U x 700W	N/A	N/A
7151.035	1.5U tool-less blanking panel, metal, grey smooth	N/A	N/A
7157.035	5U tool-less blanking panel, metal, grey smooth	N/A	N/A
9960.552	Side breathing air baffle	N/A	N/A

Fan system

Fan System			
7968.035	Fan Tray 600 x 800, 1000, 1200	5502.010	Fan mounting plate, up to (3) fans, RAL 7035
7986.035	Fan Tray 800 x 600	5502.010	Fan mounting plate, up to (3) fans, RAL 7035
7988.035	Fan Tray 800 x 800, 1000, 1200	5502.020	Fan mounting plate, up to (6) fans, RAL 7035
7966.035	Fan Tray 600 x 600	N/A	N/A

Door Control System

Door Control System			
9971.115	Door Kit	N/A	N/A

Keyboards, supports and drawers

Keyboards, supports and drawers			
7281.035	Keyboard Drawer 2U	5502.305	19", 2 U, Pull-out drawer

Rittal – The System.

Faster – better – worldwide.

- Enclosures
- Power Distribution
- Climate Control
- IT Infrastructure
- Software & Services

The Rittal Corporation is the U.S. subsidiary of Rittal GmbH & Co. KG and manufactures the world's leading industrial and IT enclosures, racks and accessories, including climate control and power management systems for industrial, data center, outdoor and hybrid applications. For more information about Rittal and its products, please visit www.rittal.us or call 1-800-477-4000.

Rittal Corporation

1 Rittal Place • Urbana Ohio 43078 • USA
Woodfield Corporate Center • 425 North Martingale Road, Suite 400 • Schaumburg Illinois 60173 • USA
Phone: 937-399-0500 • Fax: 800-477-4003 • Toll-free: 800-477-4000
Email: rittal@rittal.us • Online: www.rittal.us

Rittal Systems Ltd.

6485 Ordan Drive • Mississauga Ontario L5T 1X2 • Canada
Phone: 905-795-0777 • Fax: 905-795-9548 • Toll-free: 800-399-0748
Email: marketing@rittal.ca • Online: www.rittal.ca

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP