

**Blue e+ Wall-mounted Air Conditioners**

- UL Type 12
- 6,000–20,000 BTU
- Energy Efficient
- Touch Screen Controller
- Nanocoated Condenser
- Multi-Voltage



**Top Therm Air-to-Water Heat Exchangers**

- UL Type 12
- Thermal Output 17.5–90 w/k
- Roof-and Wall-mounted Versions
- 115V, 230V, 400V, 3~
- Intelligent Comfort Controller
- Energy Efficient
- Maintenance Free
- Optimal for Extreme Ambient Conditions



**Top Therm Chillers**

- Centralized, Efficient Cooling Using Water
- 3,412–150,000 BTU
- Intelligent Comfort Controller
- Nanocoated Condenser
- Ideal for Machine and Enclosure Cooling
- Multi-Voltage



**Enclosure Heaters**

- Positive Temperature Coefficient (PTC) Technology
- UL Type 12
- Thermal Output 30–2700 BTU
- Maintenance Free Design



**Rittal – The System.**

Faster – better – everywhere.

- Enclosures
- Power Distribution
- Climate Control
- IT Infrastructure
- Software & Services



For more information about the entire line of Rittal climate control products scan the QR Code at left or visit [www.rittalenclosures.com/climate-control](http://www.rittalenclosures.com/climate-control)

**Rittal North America LLC**

Woodfield Corporate Center  
425 North Martingale Road, Suite 400  
Schaumburg, Illinois 60173 • USA  
Phone: 937-399-0500 • Toll-free: 800-477-4000  
Email: [rittal@rittal.us](mailto:rittal@rittal.us) • Online: [www.rittal.us](http://www.rittal.us)

**Rittal Systems Ltd.**

6485 Ordan Drive  
Mississauga, Ontario L5T 1X2 • Canada  
Phone: 905-795-0777 • Toll-free: 800-399-0748  
E-Mail: [marketing@rittal.ca](mailto:marketing@rittal.ca) • Online: [www.rittal.ca](http://www.rittal.ca)

**Rittal Mexico**

Dr. Roberto Gayol 1219–1B  
Col. Del Valle Sur, 03100 • Mexico, D.F.  
Phone: (+52) (55) 5559-5369  
Toll-free: 01 800 8 Rittal (748.825)  
E-Mail: [info@rittal.com.mx](mailto:info@rittal.com.mx)  
Website: [www.rittal.com.mx](http://www.rittal.com.mx)

**Rittal – The System.**

Faster – better – everywhere.

**Climate Control Quick Reference**



03/18 ■ US295



**Filter Fans**

- UL Type 12
- UL Type 3R, 4, 4X, with optional Hose-proof Hood
- 12–529 CFM
- Tool-less Assembly
- Reversible/Diagonal Fan Motor
- Roof-Top Design Available



**Top Therm Air-to-Air Heat Exchanger**

- 34–2,730 BTU
- 115V and 230V Available
- Quick-connecting Terminals
- Available With or Without Fans



**Thermoelectric Coolers**

- Uses the Peltier Effect
- 341 BTU
- Compact, Lightweight, Efficient
- Multiple Mounting Positions
- 24V DC or dual 100–240V option



**Top Therm Blue e Wall-mounted Air Conditioners**

- UL Type 12
- 1,000–15,000 BTU
- Available in Carbon Steel or 316 Stainless Steel 4X
- Nanocoated Condenser
- Integrated Condensate Evaporator
- Multiple Mounting Positions



# Climate Control Quick Reference

## Blue e UL Type 12 Wallmount Carbon Steel Air Conditioners

Part No.	Description
3302.100	1296 BTU, 230V, 60Hz, Basic Controller
3302.110	1296 BTU, 115V, 60Hz, Basic Controller
3303.500	2252 BTU, 230V, 50/60Hz, Comfort Controller
3303.510	2252 BTU, 115V, 60Hz, Comfort Controller
3304.500	3753 BTU, 230V, 50/60Hz, Comfort Controller
3304.510	3753 BTU, 115V, 50/60Hz, Comfort Controller
3304.540	3753 BTU, 460V, 3~, 50/60Hz, Comfort Controller
3305.500	6005 BTU, 230V, 50/60Hz, Comfort Controller
3305.510	6005 BTU, 115V, 50/60Hz, Comfort Controller
3305.540	5493 BTU, 460V, 3~, 50/60Hz, Comfort Controller
3328.500	8735 BTU 230V, 50/60Hz, Comfort Controller
3328.510	8735 BTU 115V, 50/60Hz, Comfort Controller
3328.540	8700 BTU 460V, 3~, 50/60Hz, Comfort Controller
3329.500	9246 BTU 230V, 50/60Hz, Comfort Controller
3329.510	9246 BTU 115V, 50/60Hz, Comfort Controller
3329.540	9383 BTU 460V, 3~, 50/60Hz, Comfort Controller
3332.540	13477 BTU 460V, 3~, 50/60Hz, Comfort Controller
Accessories	
3286.310	Metal Filter for 3302.xxx, 3303.xxx
3286.410	Metal Filter for 3304.xxx, 3305.xxx, 3328.xxx, 3329.xxx, 3332.540
3286.300	Foam Filter (PU 3) for 3302.xxx, 3303.xxx
3286.400	Foam Filter (PU 3) for 3304.xxx, 3305.xxx, 3328.xxx, 3329.xxx, 3332.540

## Blue e+ UL Type 12 Wallmount Carbon Steel Air Conditioners

Part No.	Description
3185.830	AC 5119 BTU Multivoltage 50-60HZ Type 12
3186.930	AC 6830 BTU Multivoltage 50-60HZ Type 12
3187.930	AC 8879 BTU Multivoltage 50-60HZ Type 12
3188.940	AC 14343 BTU 380-480V 3PH 50-60HZ Type 12
3189.940	AC 19808 BTU 380-480V 3PH 50-60HZ Type 12
Accessories	
3285.900	Foam Filter (PU=3) for 3186.XXX, 3187.XXX, 3188.XXX, 3189.XXX
3285.910	Metal Filter (PU=1) for 3186.XXX, 3187.XXX, 3188.XXX, 3189.XXX
3124.400	External Temperature Sensor with Connection Cable

## UL Type 4/4X Wallmount Stainless Steel Air Conditioners

Part No.	Description
3303.504	2252 BTU, 230V, 50/60Hz, Comfort Controller
3303.514	2252 BTU, 115V, 60Hz, Comfort Controller
3304.504	3753 BTU, 230V, 50/60Hz, Comfort Controller
3304.514	3753 BTU, 115V, 60Hz, Comfort Controller
3304.544	3753 BTU, 460V, 3~, 50/60Hz, Comfort Controller
3305.504	6005 BTU, 230V, 50/60Hz, Comfort Controller
3305.514	6005 BTU, 115V, 60Hz, Comfort Controller
3305.544	5493 BTU, 460V, 3~, 50/60Hz, Comfort Controller
3328.504	8735 BTU, 230V, 50/60Hz Comfort Controller
3328.514	8735 BTU, 115V, 50/60Hz Comfort Controller
3328.544	8700 BTU, 460V, 3~, 50/60Hz Comfort Controller
3329.504	9246 BTU, 230V, 50/60Hz Comfort Controller
3329.514	9246 BTU, 115V, 50/60Hz Comfort Controller
3329.544	9383 BTU, 460V, 3~, 50/60Hz Comfort Controller
Accessories	
3286.310	Metal Filter for 3303.xxx
3286.410	Metal Filter for 3304.xxx, 3305.xxx, 3328.xxx, 3329.xxx
3286.300	Foam Filter (PU 3) for 3303.xxx
3286.400	Foam Filter (PU 3) for 3304.xxx, 3305.xxx, 3328.xxx, 3329.xxx



## UL Type 12 Roofmount Carbon Steel Air Conditioners

Part No.	Description
3382.500	2115 BTU 230V, 50/60Hz, Comfort Controller
3382.510	2115 BTU 115V, 50/60Hz, Comfort Controller
3383.500	3719 BTU 230V, 50/60Hz, Comfort Controller
3383.510	3719 BTU 115V, 50/60Hz, Comfort Controller
3383.540	3719 BTU 400V, 2~, 50/60Hz, Comfort Controller
3384.500	5630 BTU 230V, 50/60Hz, Comfort Controller
3384.510	5630 BTU 115V, 50/60Hz, Comfort Controller
3384.540	5630 BTU 400V, 2~, 50/60Hz, Comfort Controller
3385.500	7301 BTU 230V, 50/60Hz, Comfort Controller
3385.510	7301 BTU 115V, 50/60Hz, Comfort Controller
3385.540	7301 BTU 400V, 2~, 50/60Hz, Comfort Controller
3386.540	11260 BTU 460V, 3~, 50/60Hz, Comfort Controller
3387.540	13648 BTU 460V, 3~, 50/60Hz, Comfort Controller
Accessories	
3286.510	Metal Filter for 3382.xxx, 3383.xxx, 3384.xxx, 3385.xxx
3286.610	Metal Filter for 3386.540, 3387.540
3286.500	Foam Filter (PU 3) for 3382.xxx, 3383.xxx, 3384.xxx, 3385.xxx
3286.600	Foam Filter (PU 3) for 3386.540, 3387.540

## UL Type 12 Filter Fans

Part No.	Description
3237.100	12/15 CFM, 230V, 50/60Hz
3237.110	12/15 CFM, 115V, 50/60Hz
3237.124	12 CFM, 24V DC
3238.100	32/39 CFM, 230V, 50/60Hz
3238.110	32/39 CFM, 115V, 50/60 Hz
3238.124	32 CFM, 24V DC
3239.100	62/71 CFM, 230V, 50/60 Hz
3239.110	62/71 CFM, 115V, 50/60 Hz
3239.124	62 CFM, 24V DC
3240.100	106/94 CFM, 230V, 50/60 Hz
3240.110	106/94 CFM, 115V, 50/60 Hz
3240.124	106 CFM, 24V DC
3241.100	135/147 CFM, 230V 50/60 Hz
3241.110	135/147 CFM, 115V, 50/60 Hz
3241.124	135 CFM, 24V DC
3243.100	324/353 CFM, 230V, 50/60 Hz
3243.110	324/353 CFM, 115V, 50/60 Hz
3244.100	412/454 CFM, 230V, 50/60 Hz
3244.110	412/453 CFM, 115V, 50/60 Hz
3244.140	412/453 CFM, 400/460V, 3~, 50/60 Hz
Accessories	
3237.200	Exhaust Filter for 3237.xxx
3238.200	Exhaust Filter for 3238.xxx
3239.200	Exhaust Filter for 3239.xxx
3240.200	Exhaust Filter for 3240xxx, 3241xxx
3243.200	Exhaust Filter for 3243.xxx, 3244.xxx
3237.085	Carbon Steel Rain Hood, UL Type 4 for 3237.xxx
3238.085	Carbon Steel Rain Hood, UL Type 4 for 3238.xxx
3239.085	Carbon Steel Rain Hood, UL Type 4 for 3239.xxx
3240.085	Carbon Steel Rain Hood, UL Type 4 for 3240.xxx, 3241.xxx
3243.085	Carbon Steel Rain Hood, UL Type 4 for 3243.xxx, 3244.xxx
3237.080	Stainless Steel Rain Hood, UL Type 4X for 3237.xxx
3238.080	Stainless Steel Rain Hood, UL Type 4X for 3238.xxx
3239.080	Stainless Steel Rain Hood, UL Type 4X for 3239xxx
3240.080	Stainless Steel Rain Hood, UL Type 4X for 3240.xxx, 3241.xxx
3243.080	Stainless Steel Rain Hood, UL Type 4X for 3243.xxx, 3244.xxx

## Rittal Service Contracts

### The Ultimate Back-Up

Rittal offers a choice of four standard service packages, available worldwide. Just choose the level of service which best meets your needs or let us design a customized service package. **Connect with Rittal: 1-800-477-4000, extension #3 or service@rittal.us**

Package	Availability	Response Time	Spare Parts	Maintenance	Warranty Extension
BASIC	Business Hours	Next Working Day	Standard	1 x/year	No
COMFORT	Business Hours	Next Day	Standard	2 x/year	No
ADVANCED	24 Hours 365 Days/Year	Next Day	24 Hours	2 x/year	Yes
FULL	24 Hours 365 Days/Year	8 Hours	As Agreed	As Agreed (At Least 2 x/year)	Yes
CUSTOMIZED	As Agreed	As Agreed	As Agreed	As Agreed	As Agreed