



## Product conversion of AX base/plinth system

### Conversion table

Please note that the design concept has changed. The new AX base/plinth system does not require corner pieces. Instead, panels are used at the front and rear, while a base/plinth element is installed in the depth.

AX base/plinth corner pieces with trim panels, front and rear, height 100 mm		AX base/plinth trim panels, front and rear, height 100 mm	
Model No. OLD	To fit width mm	Model No. NEW	To fit width mm
2820.061	600	2830.061	600
2820.081	800	2830.081	800
2820.101	1000	2830.101	1000
2820.121	1200	2830.121	1200

AX base/plinth corner pieces with trim panels, front and rear, height 200 mm		AX base/plinth trim panels, front and rear, height 200 mm	
Model No. OLD	To fit width mm	Model No. NEW	To fit width mm
2820.062	600	2830.062	600
2820.082	800	2830.082	800
2820.102	1000	2830.102	1000
2820.122	1200	2830.122	1200

AX base/plinth trim panels, side, height 100 mm		AX base/plinth components, side, height 100 mm	
Model No. OLD	To fit depth mm	Model No. NEW	To fit depth mm
2820.310	300	2830.310	300
2820.410	400	2830.410	400

AX base/plinth trim panels, side, height 200 mm		AX base/plinth components, side, height 200 mm	
Model No. OLD	To fit depth mm	Model No. NEW	To fit depth mm
2820.320	300	2830.320	300
2820.420	400	2830.420	400