

Conversion tool for EC fan-and-filter units

Description	Air throughput	Rated operating voltage	RAL	Model No. (old)	Model No. NEW
Blue e+ EC- fan-and-filter unit	63 m³/h	230 V	7035	3238.500	3238.700*
	110 m³/h	230 V	7035	3239.500	3239.700*
	218 m³/h	100 – 240 V	7035	3240.500	3240.900
	272 m³/h	100 – 240 V	7035	3241.500	3241.900
	625 m³/h	100 – 240 V	7035	3243.500	3243.900
	867 m³/h	100 – 240 V	7035	3244.500	3244.900
	1,161 m³/h	230 V	7035	3245.500	3245.900
		115 V		3245.510	3245.910
		230 V	9005	3245.508	3245.908
		115 V		3245.518	3245.918

*Not available as EC option. You may use the standard option as an alternative.

Conversion tool for outlet filters

Description	To fit fan-and-filter units	RAL / option	Model No. (old)	Model No. NEW
Blue e+ outlet filter	3238.xxx	7035	3238.200	3238.300
	3239.xxx	7035	3239.200	3239.300
	3240./3241.xxx	7035	3240.200	3240.300
	3243./ 3244./ 3245.xxx	7035	3243.200	3243.300
		9005	3243.208	3243.308