

Rittal – The System.

Faster – better – everywhere.

► Outdoor wall-mounted enclosures – CS 9791.035

Date : Sep 25, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Outdoor wall-mounted enclosures – CS 9791.035

created: 25.09.2020 build on www.rittal.com/lt-en



Product description

Description: Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out in the bottom and integrated louvres on the rear panel and side panels for ventilation.

Material: Enclosure: Aluminium AlMg3
Door: Stainless steel 1.4301 (AISI 304), 1.5 mm
Mounting plate: Aluminium, 2 mm

Surface finish: Enclosure: Powder-coated, UV-resistant pure polyester
Mounting plate: Clear chromated

Colour: RAL 7035

**Protection category
IP to IEC 60 529:** IP 55

Supply includes: Double-walled outdoor enclosure, fully preconfigured
Inner enclosure with mounting plate, gland plate and security lock
Mounting bracket for enclosure internal thermostat or hygostat
Outer enclosure with designer cover and security lock 3524 E
2 C rails on the rear panel

Note: Extended delivery times.

Basic material: Aluminium

Product features

Dimensions: Width: 530 mm
Height: 700 mm
Depth: 265 mm

Clearances:	Clearance width: 440 mm Clearance height: 545 mm Clearance depth: 195 mm
Mounting plate:	Width: 430 mm Height: 535 mm
Inner enclosure:	Width: 460 mm Height: 565 mm Depth: 220 mm
Lock version:	Cam
Number of locks:	2
Packs of:	1 pc(s).
Weight/pack:	14.86 kg
EAN:	4028177193710
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	CS Wall-mounted enclosure, WHD: 530x700x265 mm, aluminum, with mounting plate, Enclosure-within-an-enclosure concept
Approvals	
Declarations:	Declaration of conformity