

Rittal – The System.

Faster – better – everywhere.

► Terminal boxes KL with gland plate – KL 1539.510

Date : Mar 3, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Terminal boxes KL with gland plate – KL 1539.510

created: 03.03.2021 build on www.rittal.com/nz-en



Discontinued article.

This item will be discontinued on: 30.09.2020 |||This item is being replaced by: 1539000

Product description

Material:	Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal
Surface finish:	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
IK Code:	IK08
Supply includes:	Enclosure with cover Quick-release fastener including plastic bushes Sheet steel gland plates with seals and assembly parts
Basic material:	Sheet steel

Product description

Dimensions:	Width: 400 mm Height: 400 mm Depth: 120 mm
Material thickness:	Enclosure: 1.38 mm

Cover: 1.25 mm

Gland plates:	Size/Qty. (top/bottom): 2 / 1 + 1 Size/Qty. (left/right): 2 / 1 + 1
Packs of:	1 pc(s).
Weight/pack:	6.7 kg
EAN:	4028177251601
Customs tariff number:	73269098
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	KL Terminal box, WHD: 400x400x120 mm, Sheet steel, without mounting plate, with cover, with gland plate
Approvals	
Approvals:	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL
Certificates:	IK-Code NA Protection category
Declarations:	Declaration of conformity