

Rittal – The System.

Faster – better – everywhere.

Comfort Panel – CP 6372.541

Date : Oct 1, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Comfort Panel – CP 6372.541

created: 01.10.2020 build on www.rittal.com/nz-en



Product description

Design:	Support arm connection, rectangular 120 x 65 mm
Benefits:	Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material:	Enclosure: Extruded aluminium section Corner pieces: Die-cast zinc Corner protectors: Plastic
Colour:	Enclosure: Natural anodised. Corner pieces: RAL 7035 Corner protectors: similar to RAL 7024
Protection category IP to IEC 60 529:	IP 65
Protection category NEMA:	NEMA 12
Supply includes:	Enclosure with cut-out for support arm connection 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Seals and assembly parts for front panels Hinged rear panel, hinging on the longest side
Note:	The support arm connection may be swapped over by rotating the enclosure

Product features

For the configuration of subracks:	To fit front panel width: 520 mm
---	----------------------------------

Installation depth:	74 mm
To fit front panels:	with width: 520 mm with height: 400 mm
Lock version:	Screw lock
Packs of:	1 pc(s).
Weight/pack:	7.8 kg
EAN:	4028177663060
Customs tariff number:	94032080
ETIM 7.0:	EC002504
ETIM 6.0:	EC002504
eCl@ss 8.0/8.1:	27180505
eCl@ss 6.0/6.1:	27180505
Product description:	CP Compact Panel, for front panel BH 520x400 mm, installation depth 74 mm, Extruded aluminum section, Support arm connection 120x65 mm, Hinged rear panel with screw lock
Approvals	
Approvals:	UL + C-UL
Certificates:	Protection category
Declarations:	Declaration of conformity