

Rittal – The System.

Faster – better – everywhere.

Polycarbonate enclosures PK with knockouts – PK 9514.050

Date : Sep 23, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Polycarbonate enclosures PK with knockouts – PK 9514.050

created: 23.09.2020 build on www.rittal.com/nz-en



Product description

| | |
|--|--|
| Applications: | Ambient temperature range: -35 °C...+80 °C The specified temperatures may be limited by the installed equipment |
| Material: | Enclosure: Fibreglass-reinforced polycarbonate Cover: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene |
| Colour: | RAL 7035 |
| Protection category IP to IEC 60 529: | IP 66 |
| Protection category NEMA: | NEMA 4X |
| IK Code: | IK08 |
| Supply includes: | Enclosure with cover Cover screws Insulating bungs for wall mounting screws |
| Basic material: | Polycarbonate |

Product features

| | |
|--------------------|---|
| Dimensions: | Width: 180 mm Height: 110 mm Depth: 90 mm |
|--------------------|---|

| | |
|-----------------------------------|--|
| Cover: | grey |
| Ambient temperature range: | -35 °C...+80 °C |
| Cable entry: | Number x metric diameter: 16 x M20 Number x metric diameter: 2 x M20/M25 Number x metric diameter: 2 x M32/M40 |
| Packs of: | 2 pc(s). |
| Weight/pack: | 0.86 kg |
| EAN: | 4028177490208 |
| Customs tariff number: | 94037000 |
| ETIM 7.0: | EC000261 |
| ETIM 6.0: | EC000261 |
| eCl@ss 8.0/8.1: | 27180101 |
| eCl@ss 6.0/6.1: | 27180101 |
| Product description: | PK Polycarbonate enclosure, WHD: 180x110x90 mm, fibreglass-reinforced polycarbonate, with knockouts, with grey cover |
| Approvals | |
| Approvals: | C-UL DNV-GL UL |
| Declarations: | Declaration of conformity |