Rittal – The System.

Faster – better – everywhere.





EL 2261.605 Wall-mounted enclosures EL, 3-part

State: 8/12/2025 (Source: rittal.com/au-en)



EL 2261.605 - Wall-mounted enclosures EL, 3-part with mounting plate and mounting angles, static installation

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top and bottom, mounting plate is supplied loose. Protection category IP 55.

Features

Model No.	EL 2261.605		
Design	Wall-mounted enclosures IT		
	with mounting plate and mounting angles, static installation		
Product description	Wall-mounted enclosure with optimum accessibility due to hinged part.		
Material	Wall and hinged part: Sheet steel, 1.5 mm		
	Viewing window: Single-pane safety glass, 3 mm		
Surface finish	Powder-coated		
General colour	RAL 7035		
Colour	Wall and hinged part: RAL 7035		
	Glazed door: RAL 7035/7015 (slate grey)		
Supply includes	Wall section with solid gland plate, top and bottom and mounting		
	plate (supplied loose).		
	Hinged part with 25 mm pitch pattern of holes in the front and rear		
	frame, and two 482.6 mm (19") mounting angles, front, static		
	installation		
	Designer glazed door		
	1 double-kit key no. 5		
	Comfort handle for lock inserts and 2-point locking		
	Security lock 3524 E		
Units	21 U		
Dimensions	Width: 600 mm		
	Height: 1,012 mm		
	Depth: 373 mm		
Installation depth	320 mm		

© Rittal 2025

2

Features

Clearance width: 502 mm Clearance height: 949 mm
216 mm
485 mm x 965 mm
135 mm
IK08
750 N
Sheet steel
IP 55
1 pc(s).
50.35
53
94032080
4028177324367
EC002500
EC002500
27180208

Approvals

Approvals	Lloyds Register of Shipping	
	UL + C-UL (listed)	

© Rittal 2025 3

Tender text

Wall-mounted enclosure Electronic Kombi System, preconfigured, 21 U

Enclosure: 3-part wall-mounted enclosure consisting of: Wall section with solid gland plate at the top and bottom, may optionally be exchanged for cable entry variants (accessories), holes for wall-mounting, 1 mounting plate (supplied loose) Hinged section with 2 mounting angles, 482.6 mm (19 inch), fitted at the front, with all-round 25 mm pitch pattern of holes in the front and rear frame, designer glazed door with mini comfort handle for lock inserts, with security lock 3524 E, may optionally be exchanged for mini comfort handle for semi cylinder

Protection category: IP 55 to EN 60 529/10.91

Load capacity of hinged part: 75 kg

Material

Enclosure: 1.5 mm sheet steel

Mounting plate: 2.5 mm sheet steel Viewing window: 3 mm safety glass

Surface finish

Electrophoretic dipcoat-primed, spray-finished,

enclosure in RAL 7035, glazed door in RAL 7035/7015,

zinc-plated mounting plate

Dimensions (W x H x D): 600 x 1012 x 373 mm (21 U)

© Rittal 2025 4