

Rittal – The System.

Faster – better – everywhere.



SZ 2311.225

Spacers

State: 4/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2311.225 - Spacers

The universal assembly component for all situations where a distance from the mounting level is required.

Features

| | |
|-------------------------------|---|
| Model No. | SZ 2311.225 |
| Product description | The universal assembly component for all situations where a distance from the mounting level is required. |
| Technical specifications | With self-tapping thread for 4.5 mm dia. holes |
| Material | Hexagonal steel (SW8) |
| Surface finish | Zinc-plated |
| Length | 25 mm |
| Assembly instruction | Top-hat rails/cross rails, contact hazard protection covers, master switch trim panels, cable clamp rails etc. may be attached to the rear with metal screws 5.5 x 13 |
| Packs of | 12 pc(s). |
| Net weight | 0.108 kg |
| Gross weight | 0.118 kg |
| PCF per pack (cradle-to-gate) | 0.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73181535 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Spacer, L: 25 mm |