

Rittal – The System.

Faster – better – everywhere.



AE 2383.250

Rail for interior installation

State: 3/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 2383.250 - Rail for interior installation for AE/WM

For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



Features

Model No.	AE 2383.250
Product description	For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g. for: TS punched section, enclosure lights, door-operated switch, door stay, cable conduit holder
Material	Sheet steel
Surface finish	Zinc-plated
Note	Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000
To fit	Enclosure type: AE Depth: = 250 mm
Packs of	4 pc(s).
Net weight	0.72 kg
Gross weight	0.8 kg
Customs tariff number	73269098
ETIM 9	EC002625
ETIM 8	EC002625

Features

ECLASS 8.0

27189234

Product description

AE Rail for interior installation, for AE, for D: 250 mm