

Rittal – The System.

Faster – better – everywhere.



AE 2383.300

Rail for interior installation

State: 4/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 2383.300 - Rail for interior installation for AE/WM

For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



Features

| | |
|-----------------------|--|
| Model No. | AE 2383.300 |
| Product description | For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g. for: TS punched section, enclosure lights, door-operated switch, door stay, cable conduit holder |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Note | Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000 |
| To fit | Enclosure type: AE Depth: = 300 mm |
| Packs of | 4 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 0.92 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |

Features

ECLASS 8.0

27189234

Product description

AE Rail for interior installation, for AE, for D: 300 mm