

# Rittal – The System.

Faster – better – everywhere.



## SZ 2388.050

## Rail

State: 9/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2388.050 - Rail for EMC shielding bracket and strain relief

Combined rail for strain relief and EMC contacting of inserted cables.



## Features

|                      |  |
|----------------------|--|
| Model No.            | SZ 2388.050  |
| Design               | C rail to accommodate cable clamps<br>T-head cut-outs on a 40 mm pitch pattern for cable clamping using cable ties                                     |
| Product description  | Combined rail for strain relief and EMC contacting of inserted cables.   |
| Benefits             | Additional contacting on the left or right of the rail via existing holes (9 mm diameter)<br>Prepared for tool-free mounting of EMC shielding brackets |
| Material             | Extruded aluminium section   |
| Surface finish       | Chromium-free passivated   |
| Supply includes      | 1 rail<br>2 retaining brackets<br>Assembly parts   |
| Length               | 953 mm   |
| Installation options | on the horizontal/vertical enclosure section<br>may also be fitted without a retaining bracket on a mounting plate                                     |
| To fit               | Enclosure type: VX<br>TS<br>Width: = 1,000 mm  |
| Packs of             | 1 pc(s).   |

# Features

---

|                       |  |
|-----------------------|--|
| Net weight            | 0.76 kg  |
| Gross weight          | 0.84 kg  |
| Customs tariff number | 76042990   |
| ETIM 9                | EC002625   |
| ETIM 8                | EC002625   |
| ECLASS 8.0            | 27189234   |
| Product description   | SZ Rail, for EMC rail and stain relief, for W: 1000 mm |

---