Rittal – The System.

Faster – better – everywhere.





SZ 2561.300 Plastic gland plate

State: 7/12/2025 (Source: rittal.com/au-en)



SZ 2561.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

Model No.	SZ 2561.300	
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.	
Material	Plastic to UL 94-V0	
Colour	Similar to RAL 7035	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	
Dimensions	Width: 256 mm Depth: 149 mm	
To fit	Enclosure type: AX	
Gland plate	Size: 1	
Protection category to IEC 60 529	IP 66 if installed correctly	
Type rating to UL 50E	Type 1 Type 12	
No. of cable entries and Ø (mm) minmax.	15 x 5-11 22 x 10-15 8 x 15-25 4 x 19-34 1 x 26-54	
Packs of	1 pc(s).	
Net weight	0.36	
Gross weight	0.365	
Customs tariff number	39269097	
EAN	4028177935693	
E-Number Sweden	E3465288	

© Rittal 2025

Features

ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3