


**Rittal – The System.**

Faster – better – everywhere.



**SZ 2563.500**

**Plastic cable gland plates**

State: 24/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2563.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

## Features

|  |   |
|--|---|
| Model No.                                    | SZ 2563.500   |
| Product description                          | Simply pierce the plastic with a sharp object, and pull through the cable.                            |
| Material                                     | Plastic to UL 94-V0<br>Halogen free   |
| Colour                                       | Similar to RAL 7035   |
| Note   | The allocation of gland plate sizes is indicated on the relevant enclosures                           |
| Dimensions                                   | Width: 534 mm<br>Depth: 149 mm  |
| To fit                                       | Enclosure type: AE  |
| Gland plate                                  | Size: 5   |
| Protection category to IEC 60 529            | IP 65   |
| No. of cable entries and Ø (mm)<br>min.-max. | 18 x 5-9<br>16 x 7-12<br>36 x 10-15<br>6 x 15-24<br>2 x 23-30<br>2 x 26-35<br>4 x 26-54<br>1 x 50-110 |
| Packs of                                     | 1 pc(s).  |
| Net weight                                   | 0.86  |
| Gross weight                                 | 0.96  |
| Customs tariff number                        | 39269097  |
| EAN  | 4028177325616   |

# Features

|                 |          |
|-----------------|----------|
| E-Number Sweden | E3404729 |
| ETIM 9          | EC000211 |
| ETIM 8          | EC000211 |
| ECLASS 8.0      | 27142421 |