

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2564.200**

**Plastic gland plate, modular**

State: 23/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2564.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).



## Features

Model No.	SZ 2564.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Colour	RAL 7035
Number of rectangular cutouts information	1 rectangular cut-out can hold 10 small seal inserts
Number of rectangular cutouts	6
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	5 x M12 4 x M16 6 x M20 5 x M25 1 x M32 1 x M40

# Features

Dimensions	Width: 534 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 4
Operating temperature range	-40 °C...80 °C
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12
Packs of	1 pc(s).
Net weight	0.54 kg
Gross weight	0.573 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Plastic gland plates, for AX, for cable entry, modular, pre-punched, WD: 534x149 mm, for gland plates size 4

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------