



SZ 2566.450 - Two-part gland plate with foam rubber cable clamp strip for AX

The divided gland plate supports simple mounting on the enclosure and offers a range of different installation options. For simple insertion of cables with and without connectors into the enclosure. Special drilled holes in the gland plate ensure automatic potential equalisation during screw-fastening. Bolts, clips and earthing cables are no longer required.

Features

| | |
|------------------|---|
| Model No. | SZ 2566.450 |
| Design | two-piece |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures When installing in enclosure width >760 mm, 2 packs are required |
| Dimensions | Width: 401 mm Depth: 221 mm |
| To fit | Enclosure type: AX |
| To fit Model No. | 1110.000 1114.000 1130.000 1213.000 1350.000 1115.000 1214.000 |
| Gland plate | Size: 6 |
| Packs of | 1 pc(s). |
| Net weight | 1.3 kg |
| Gross weight | 1.36 kg |

Features

| | |
|-------------------------------|---|
| PCF per pack (cradle-to-gate) | 5.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, two-part, for AX, with foam rubber cable clamp strip, WD 401x221 mm, for gland plate size 6 |