Rittal – The System.

Faster – better – everywhere.





AX 2572.100 Metal gland plate

State: 7/12/2025 (Source: rittal.com/au-en)



AX 2572.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

Model No.	AX 2572.100	
Product description	Simply knock out the holes for the cable glands using a screwdrive	
Material	Sheet steel	
Colour	RAL 7035	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	
No. of metric knockouts	6 x M16	
	4 x M20	
	10 x M25	
	2 x M32	
	2 x M40	
Dimensions	Width: 339 mm	
	Depth: 149 mm	
To fit	Enclosure type: AX	
Gland plate	Size: 2	
Protection category to IEC 60 529	IP 66 if installed correctly	
Type rating to UL 50E	Type 1	
	Type 12K	
Number knockouts	6	
	4	
	10	
	2	
	2	

© Rittal 2025

Features

Metric diameter	M16	
	M20	
	M25	
	M32	
	M40	
Packs of	1 pc(s).	
Net weight	0.6	
Gross weight	0.605	
PCF per pack (cradle-to-gate)	3 kg CO2 eq (Cat B)	
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared	
Customs tariff number	73079100	
EAN	4028177925236	
E-Number Sweden	E3465296	
ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

Approvals

Approvals	UL + C-UL - FTTA	

© Rittal 2025 3