

Rittal – The System.

Faster – better – everywhere.



AX 2576.100 Metal gland plate

State: 22/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2576.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

| | |
|-----------------------------------|---|
| Model No. | AX 2576.100 |
| Product description | Simply knock out the holes for the cable glands using a screwdriver. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 2 x M12 10 x M16 8 x M20 18 x M25 4 x M32 4 x M40 |
| Dimensions | Width: 401 mm Depth: 221 mm |
| To fit | Enclosure type: AX |
| Gland plate | Size: 6 |
| Protection category to IEC 60 529 | IP 66 if installed correctly |
| Type rating to UL 50E | Type 1 Type 12K |
| Packs of | 1 pc(s). |
| Net weight | 1.07 kg |
| Gross weight | 1.073 kg |
| PCF per pack (cradle-to-gate) | 5.4 kg CO2 eq (Cat B) |

Features

| | |
|-----------------------|--|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, for AX, with metric knockouts, WD: 401x221 mm, for gland plates size 6 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|