

# Rittal – The System.

Faster – better – everywhere.



## FT 2735.590 System windows

State: 25/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2735.590 - System windows for VX, TS, VX SE

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.



## Features

|                     |   |
|---------------------|---|
| Model No.           | FT 2735.590   |
| Design              | 30 section  |
| Product description | To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.   |
| Material            | Extruded aluminium section with die-cast zinc corner pieces and single-pane safety glass.   |
| Surface finish      | Base frame: Powder-coated on the outside in RAL 7035<br>Hinge and lock section: Natural-anodised  |
| Value base frame    | Made from single-pane safety glass: High level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Hinge with 180° opening angle, easily inserted. |

# Features

|                                   |   |
|-----------------------------------|---|
| Value base frame                  | Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).<br>Readily height-adjustable.<br>Stabilises the door cut-out.<br>Conceals the cut edge.<br>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.<br>Frame section height 30 mm or 60 mm |
| Protection category to IEC 60 529 | IP 54   |
| Note                              | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Not suitable for outdoor siting  |
| To fit                            | Enclosure type: VX<br>TS<br>VX SE<br>Width: = 800 mm  |
| Dimensions                        | Width: 700 mm<br>Height: 570 mm<br>Depth: 47 mm   |
| Visible area                      | Viewing window width: 563 mm<br>Viewing window height: 498 mm   |
| Build depth for components (max.) | 33 mm   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 6.105 kg  |
| Gross weight                      | 6.426 kg  |
| Customs tariff number             | 76101000  |
| ETIM 9                            | EC002527  |
| ETIM 8                            | EC002527  |
| ECLASS 8.0                        | 27182301  |
| Product description               | FT System window, for VX, TS, VX SE, 30 section, WHD: 700x570x47 mm, for W: 800 mm  |

# Approvals

---

Certificates

Protection category