

Rittal – The System.

Faster – better – everywhere.



FT 2760.010 Viewing window

State: 7/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2760.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2760.010
Design	60 section
Product description	For external mounting on AX enclosures instead of a door and on surfaces.
Material	Frame: Aluminium, natural anodised. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
To fit Model No.	1039.000 1339.000 1009.000
To fit	Enclosure type: AX Width: = 600 mm Height: = 380 mm
Dimensions	Width: 597 mm Height: 377 mm Depth: 62 mm
Visible area	Viewing window width: 537 mm Viewing window height: 317 mm

Features

Build depth for components (max.)	58 mm
Packs of	1 pc(s).
Net weight	3.245 kg
Gross weight	3.3 kg
Customs tariff number	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	FT Viewing window, WHD: 597x377x62 mm, for AX enclosures instead of the door and surfaces